


Dimensions: mm (In)

**Electrical Specifications:**

- Rating: 6A/125VAC, 3A/250VAC
- Dielectric strength: 1000VAC for 1 minute
- Insulation resistance: 100M Ω min. @ 500VDC
- Electrical life: 5,000 cycles

Mechanical Specifications:

- Mechanical life: 30,000 cycles
- Circuit: DPDT On-(On)

Materials:

- Frame, plate, lever: nickel plated brass
- Body: melamine-phenol
- Terminals: gold plated copper

Miniature Toggle Switch

10TF262

Mountain Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[10TF262](#)