

DO NOT SCALE
DIMENSIONS IN

METRIC

3rd ANGLE PROJECTION

NOTES:

NOTES:

1 MATERIAL: HOUSING: TERMOPLASTICO S/ FIBRA DE VIDRO V-0 COR: PRETO
CONTACT: BRONZE FOSFOROSO

MATERIAL: HOUSING: THERMOPLASTIC WITHOUT GLASS FIBER V-0 COLOR: BLACK
CONTACT: PHOSPHOROUS BRONZE

2 MATERIAL: HOUSING: TERMOPLASTICO C/ FIBRA DE VIDRO HB COR: NATURAL
CONTACT: BRONZE FOSFOROSO

MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER HB COLOR: NATURAL
CONTACT: PHOSPHOROUS BRONZE

3 0,38 µm. MIN. OURO NA AREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL
0,38 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING

4 0,76 µm. MIN. OURO NA AREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL
0,76 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING

5 1,27 µm. MIN. OURO NA AREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL
1,27 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING

6 ESTANHO SOBRE NIQUEL
TIN UNDER NICKEL

7 PONTO DE CONTATO E/ MEDIÇÃO DA CAMADA DE OURO
CONTACT POINT FOR GOLD PLATING MEASUREMENT

8 ACEITA PINO QUADRADO 0,64 x 0,64 OU REDONDO Ø 0,64
ALLOW SQUARE PIN 0,64 x 0,64 OR ROUND Ø 0,64

9 MATERIAL: HOUSING: TERMOPLASTICO C/ FIBRA DE VIDRO COR VERMELHO, V-2
CONTACT: BRONZE FOSFOROSO

MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER COLOR RED; V-2
CONTACT: PHOSPHOROUS BRONZE

		3	10	L	2 - 880584	- 1
11 OBSOLETE		6	9			9
11 OBSOLETE		6				8
		5				- 7
11 OBSOLETE		4				6
		3	2			- 5
		6				- 4
11 OBSOLETE		5				- 3
		4				- 2
		3	1	K7	880584	- 1

OTHER TREATMENT				FINISH		MATERIAL		PART REV.		PART NUMBER									
CUSTOMER DWG for REFERENCE ONLY						TOLERANCES UNLESS OTHERWISE STATED DEC. ± 0,3 ANGLES ± 1°		INS. DIA. RANGE		WIRE RANGE		SCALE							
								//		//		//							
								DR. Carlos 01/01/84						 TE Connectivity					
CHK. H 10 JUN 84 14/1/84						DESCRIPTION .. AMP SHUNT CONNECTOR ASS'Y													
L4 REV. ECO 11-023509		HC	WLS	02DEC11		DE.													
L3 REVISED PER ECO-11-005139		RK	HMR	28MAR11															
153 REVISION RECORD		DR	CHK	DATE		APP. J. M. [Signature]		DWG NO		A3 C 880584		SHEET 1072							


C 880584

C

B

A

- 10 MATERIAL: HOUSING: TERMOPLASTICO C/ FIBRA DE VIDRO V-2 COR: VERDE
CONTATO: BRONZE FOSFOROSO
- MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER V-2 COLOR: GREEN
CONTACT: PHOSPHOROUS BRONZE
- 11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



11 OBSOLETE	6			1	8
	5			1	7
	4			1	6
	3		2	1	5
	2			1	4
11 OBSOLETE	6			1	4
	5			1	3
	4			1	2
	3		1	K1	1 - 880584 - 1

OTHER TREATMENT	FINISH	MATERIAL	PART REV.	PART NUMBER
CUSTOMER DWG for REFERENCE ONLY				
TOLERANCES UNLESS OTHERWISE STATED DEC. ± 0,5 ANGLES ± 1°		INS. DIA. RANGE	WIRE RANGE	SCALE
DR. <i>Isidor</i> CHK. <i>N. W. S.</i> DE. <i>[Signature]</i>		TE Connectivity		
DESCRIPTION AMP SHUNT CONNECTOR ASS'Y		SHEET 2 of 2		
REV. 1 OF 2 SEE SHEET 1 OF 2		DWG NO. A3 C 880584		
REVISION	RECORD	DR	CHK	DATE