

Product Search

Item no...

Product Catalog

Products

[Lamps & LED-Lamps](#)

[LED lamps](#)

[StarLEDs](#)

[T6,8](#)

Markets

[Automotive](#)

[Aviation](#)

[Gaming](#)

[Illumination](#)

[Transport](#)

[Custom Projects](#)

Product details

Article: 1507125Y3



**StarLED, T6.8 LED-Lamp, 12V
AC/DC, yellow**

Description

Designation: StarLED, T6.8 LED-Lamp, 12V
AC/DC, yellow

Product range: StarLED

Optical features

Colour: yellow

Dominant Wavelength: 587 nm

Number of LEDs: 1

Typ. Luminous intensity: 350 mcd (at DC current)

Electrical features

Operating Voltage: 12 V

Voltage type: AC/DC

Rectifier: Half wave

Voltage tolerance: 10 %

DC current: 17 mA

Mechanical features

Socket: T6.8

Lamp size: T6.8

Length: 43 mm

Diameter: 6,8 mm

Thermal features

Operating temperature: -20...+60 °C

Storage temperature: -25...+80 °C

Gallery

Latest News

2013-01-08
LEDS MADE EASY.
>> [More details](#)

2012-03-09
Successful
surveillance audit
according to ISO
9001:2008
>> [More details](#)

2012-02-24
Latest Nichia LEDs in
CML products
>> [More details](#)



[Standard Image](#)

[Drawing](#)

[Image](#)

Click on a small picture to select it. Click the large image to view full size.



Flashing BA9s LED Lamps

You need a flashing switch in your application?
Just exchange the lamp and its done !

