

Technical Datasheet

Elecolit[®] 325



Product Description

Panacol Elecolit[®] adhesives are solvent free single or two-component adhesives. They are mostly based on epoxy resin and can be cured at room temperature or by exposure of heat. Elecolit[®] adhesives are electrically and / or thermally conductive adhesives which are designed for potting, bonding or contacting of conductors.

Elecolit[®] 325 is a silver-filled, solvent-free 2-component epoxy resin adhesive. Elecolit[®] 325 can be used with dispenser or punch. Very short curing times are possible at elevated temperatures. Elecolit[®] 325 is characterized by good conductivity values in "cold hardening" and good gap filling capacity.

Curing Properties

This product is a two-component adhesive. The adhesive can be cured at room temperature or thermally under exposure to heat after mixing the two components in the ratio indicated. Possible curing temperatures are listed in the table below.

Thermal curing	
Time at 25°C	16 h
Time at 50°C	2 h
Time at 100°C	30 min
Time at 120°C	15 min
Time at 150°C	5 min

The adhesive can be applied after mixing the components within the pot life. To determine the pot life, the time it takes to double the increase in viscosity after mixing of the two components is used.

Curing	
Pot life	2 h
Mixing ratio	1:1

The curing times given are guidelines. They refer to the curing of 2 g of adhesive. The heating up of the joining members are not taken into account. The final strength of the adhesive is reached at the earliest after 24 h.

Technical Data

Resin	epoxy
Appearance	grey
Filler	silver
Filler – weight [%]	71
Particle size D95 [µm]	26

Uncured material

Viscosity mix [mPas]	paste-like
Density [g/cm ³] <i>PE-Norm 004</i>	3,2

Technical Datasheet

Elecolit[®] 325



Cured material

Hardness shore D <i>PE-Norm 006</i>	79
Temperature resistance [°C]	-40 - 150
Water absorption [mass %] <i>PE-Norm 016</i>	<1

Glass transition temperature DSC [°C] <i>PE-Norm 009</i>	25 - 45
Coefficient of thermal expansion [ppm/K] below Tg <i>PE-Norm 017</i>	31

Thermal conductivity [W/m*K] <i>PE-Norm 062</i>	4
Volume resistivity [Ohm*cm] <i>PE-Norm 040</i>	5,E-04

Lap shear strength (steel/steel) [MPa] Curing at room temperature <i>PE-Norm 013</i>	8
Lap shear strength (steel/steel) [MPa] Curing 15 min at 120°C <i>PE-Norm 013</i>	17

Transport/Storage/Shelf Life

Trading unit	Transport	Storage	Shelf-life*
Other packages	at room temperature max. 25°C	0°C - 10°C	at delivery min. 6 months max. 12 months

***Store in original, unopened containers!**

Instructions for Use

Surface preparation

The surfaces to be bonded should be free of dust, oil, grease or other dirt in order to obtain an optimal and reproducible bond.

For cleaning we recommend the cleaner IP[®] Panacol. Substrates with low surface energy (e.g. polyethylene, polypropylene) must be pretreated in order to achieve sufficient adhesion.

Technical Datasheet

Elecolit[®] 325



Application

Our products are supplied ready to use. Depending on packaging they can be applied by hand directly from the container or semi or fully automatically. With automated application from the cartridge the adhesive is conveyed by a compressed air-operated displacement plunger via a valve in the needle. When metering low viscosity materials from bottles the adhesive is transported by a diaphragm valve. If help is required, please contact our application engineering department.

Adhesive and substrate may not be cold and must be warmed up to room temperature prior to processing.

For safety information refer to our safety data sheet.

Disclaimer

The product is free of heavy metals, PFOS and Phthalates and is conform to the EU-Directive 2017/2102/EU "RoHS III".

THE VALUES NOTED IN THIS TECHNICAL DATA SHEET ARE TYPICAL PROPERTIES AND ARE NOT MEANT TO BE USED AS PRODUCT SPECIFICATIONS.

The information contained in this data sheet is believed to be accurate and is provided for information only. Panacol makes no representation or warranties of any kind concerning this information. It is the user's responsibility to determine the suitability of this product for any intended use. Panacol does not assume responsibility for test or performance results obtained by the user. The user assumes all risk and liability connected with the use of this product.

The user should adopt such precautions and use guidelines as may be advisable for the protection of property and persons against any hazards that may be involved in this product's handling or use. Panacol specifically disclaims any liability for consequential or incidental damages of any kind arising from the handling or use of this product.

The information contained in this Technical Data Sheet offers no assurance that the product use, application, or process will not infringe on existing patents or licenses of others. Nothing in this Technical Data Sheet transfers or grants license for the use of any patents, trade secrets, intellectual property, or confidential information that is the property of Panacol.

Except as otherwise noted, all trademarks in this document (identified as [®]) are the property of Panacol.

Contact

Panacol-Elosol GmbH
Daimlerstr. 8
61449 Steinbach
Germany
Phone.: +49 6171 6202-0
Mail: info@panacol.de
www.panacol.com

Panacol-USA, Inc.
142 Industrial Lane
Torrington CT 06790
USA
Phone: +1 860-738-7449
Mail: info@panacol-usa.com
www.panacol-usa.com

Panacol-Korea Co., Ltd.
#707, Kranz Techno, 388 Dunchon-daero
Junwon-gu, Seongnam
Gyeonggi-do, 13403 KOREA
Phone: +82 31 749 1701
Mail: info@panacol-korea.com
www.panacol-korea.com

Eleco Panacol – EFD
125, av Louis Roche
Z.A. des Basses Noëls
92238 Gennevilliers Cdx FRANCE
Tél.: +33 (0)1 47 92 41 80
Mail: eleco@eleco-panacol.fr
www.eleco-panacol.fr