


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
A1	—		A3	REVISED PER ECR-09-018681	20AUG09	VKH	RRP




ACCORDING TO DIN 46228 PART 4
ENTSPRICHT DIN 46228 TEIL 4

REMARKS:
Bemerkungen

- 1 PACKING UNIT: 1000 PIECES ON REEL
VERPACKUNGSEINHEIT: 1000 STUECK AUF SPULE
- 2 MAX. INSULATION-DIA. OF WIRE: $\phi 3.2$ mm
MAX. ISOLATIONS- ϕ DER LEITUNG: $\phi 3.2$ mm
- 3 USE STRIPPER-CRIMPER MACHINE 528343-1
BENUTZEN SIE STRIPPER-CRIMPER MASCHINE 528343-1

BLACK	1241003-1	1
COLOR	PART NUMBER	NO.

DIMENSIONS: MASSEINHEITEN mm	DWN R. Schmidt	17-DEC-97	MATERIAL PP/E-Cu		FINISH OBERFLAECHE/FARBE Sn	
	CHK W.Boeck	16-JAN-98	 Tyco Electronics Tyco Electronics AMP GmbH D - 63225 Langen			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN n. ISO 2768 - m	APVD G. Feldmeier	16-JAN-98				
	PRODUCT SPEC PRODUKTSPEZ. —	NAME TUBULAR END-SLEEVE WITH PLASTIC SLEEVE, STRIP FORM, 1.5 SQmm. ADERENDHUELSE MIT KUNSTSTOFFHUELSE, BANDWARE, 1.5 SQmm.				
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES / WINKEL ± -	APPLICATION SPEC VERARBEITUNGSSPEZ. —					
	WEIGHT GEWICHT —	A4	CAGE CODE 00779	DRAWING NO ZEICHNUNGS-NR. C- 1241003	RESTRICTED TO NUR FUEHR —	
	CUSTOMER DRAWING / KUNDENZEICHNUNG					SCALE MASSSTAB 5:1