



### Cylinders, Moulded Graduations, ISO 6706, PP



- Full range of ISO 6706 graduated cylinders in ultra clear PP.
- Very easy to read as liquids have virtually no meniscus in plastic cylinders.
- Clear moulded in graduations.
- Stable hexagonal bases with non-slip anti-suction feature.
- Robust plastic construction, safe, and unbreakable.
- NB1203 consists of one each of: 10, 25, 50, 100, 250, and 500ml beakers.

Reference	Capacity ml	O.D. mm	Height mm	Sub Div ml	Tol. ±ml
CP0010P	10	14	140	0.2	0.2
CP0025P	25	20	170	0.5	0.5
CP0050P	50	26	200	1	1
CP0100P	100	31	250	1	1
CP0250P	250	42	315	2	2
CP0500P	500	55	360	5	5
CP1000P	1000	66	440	10	10
CP2000P	2000	83	535	20	20
NB1203	Set of 6 cylinders				



Exposure to temperatures above 85°C may affect accuracy.



### Cylinders, Moulded Graduations, ISO 6706, PMP



- Full range of ISO 6706 graduated cylinders in transparent PMP.
- Steam sterilisation at 121°C does not affect accuracy.
- Easy to read moulded in graduations.
- Stable hexagonal bases with non-slip anti-suction feature.
- S.P.I. recycling codes and batch code on each cylinder.
- Very easy to read as liquids have virtually no meniscus in plastic cylinders.

Reference	Capacity ml	O.D. mm	Height mm	Sub Div ml	Tol. ±ml
CT0010P	10	14	140	0.2	0.2
CT0025P	25	20	170	0.5	0.5
CT0050P	50	26	200	1	1
CT0100P	100	31	250	1	1
CT0250P	250	42	315	2	2
CT0500P	500	55	360	5	5
CT1000P	1000	66	440	10	10
CT2000P	2000	83	535	20	20