

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020180](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway Rubber Hand Lamp with 100W, Open End Guard with Reflector, with Switch and Receptacle, 15.24m (50.0') 16/3 SOOW

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130102](#)
NEMA Configuration NEMA 5-15
Outlet Side
Overview [Hand Lamps](#)
Product Name Super-Safeway
Type Hand Lamps
UPC 78678879438

Physical

Cord Length - Primary 15.24m (50.0')
Cord Length - Secondary N/A
Depth 153.92mm (6.060")
Duty Industrial
Guard Included Yes
Guard Type Open End, Reflector
Height 311.66mm (12.270")
Length N/A
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 16/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch Yes
Voltage (Fixture) - Maximum 240V

Material Info

Engineering Number 114USB163



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130102](#) Series