

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF
BUD INDUSTRIES INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT
THE WRITTEN PERMISSION OF BUD INDUSTRIES INC. IS PROHIBITED.

DWG. NO.	HH-3570		
ISSUE	REVISIONS		
(A)	CHG'D MAT'L CALL- OUT 10-29-08 DAB		
(B)	PER ECN #10509 7-9-09 DAB		
(C)	ADD TORQUE SPEC. 8-11-11 DAB		

SCREW, M2.3 x 10mm THREAD FORMING,
ROUND HEAD, PHILLIPS RECESS, STEEL,
BLACK ANODIZED (4 PL'S, NOT SHOWN)
TIGHTEN SCREWS TO 1 IN./LBS. TORQUE MAX.


Ø .180 O.D. TYP.

.400 1.811

.293

Ø .095 I.D. TYP.

BATTERY DOOR
HOLDS (4) 'AA' BATTERIES
(CONTACT KIT IS INCLUDED)



6.574

.945

2.600

1.087

.918

.177 TALL PCB
MOUNTING BOSSES

.536

.539

SECTION A-A

7.146

6.142

3.130

2.165

2.047

2.559

MATERIAL: ABS - UL94-HB (A)

FINISH: LIGHT TEXTURE
COLOR: BLACK (HH-3570-B) OR
LIGHT GRAY (HH-3570-G)

PACKAGING: SHRINK WRAP WITH A
SELF-ADHESIVE LABEL
AFFIXED ON THE OUTSIDE.

MAXIMUM PC BOARD SIZE: 3.50 x 2.312
(WITH MAX. 0.62 COMPONENT HEIGHT)

TOLERANCES: +/- .005 BETWEEN HOLE CENTERS +/- .015 FROM SHEARED EDGE +/- .032 FROM A BENT SURFACE +/- .062 BETWEEN ASSEMBLED SURFACES UNLESS OTHERWISE SPECIFIED MATERIAL FINISH		CAD GENERATED DRAWING, DO NOT MANUALLY UPDATE	
AS NOTED		APPROVALS DRAWN DP	DATE 6/10/05
AS NOTED		CHECKED	
DO NOT SCALE DRAWING		APPROVED	

BUD INDUSTRIES INC.

GRABBER STYLE J

SIZE B	DWG. NO. HH-3570	REV.
SCALE	CAD FILE:	SHEET 1 OF 1

QTY.	USED ON

(B) .039 DEEP
SMOOTH RECESS

(B) .197 DIA BOSS WITH
.079 DIA HOLE (4)