

600A AC Analog Clamp Meter

Built-in Temperature function

To measure operating temperature of motors and other electrical devices

Features:

- Jaw opens to 1.3" (34mm)
- 50/60Hz ACA frequency response
- AC/DC Voltage, Resistance and Temperature measurement
- Pointer Lock freezes reading on display
- Zero adjust
- Complete with test leads, temperature probe, 1.5V AA battery and carrying case



Applications:

- Utility Company maintenance and installation
- Plant Maintenance
- Electrical installation and repair
- Automotive repair and testing
- Appliance insulation testing
- HVAC troubleshooting



Specifications	Range	Accuracy
AC Current	6, 15, 60, 150, 600A	±3.0%FS
AC Voltage	150, 300, 750V	±3.0%FS
DC Voltage	75V	±3.0%FS
Resistance	200kΩ	±3.0% of Scale Length
Temperature	-4 to 302°F (-20 to 150°C)	±3.0% of arc
Dimension/Weight	8.4x3.3x1.7" (214x85x43mm)/12.3oz (350g)	

Ordering Information:

AM600.....600A AC Analog Clamp Meter
AM600-NIST ..600A AC Analog Clamp Meter with NIST Certificate

