

MINIATURE LAMP (161) Details



Part #	161				
Description	T3 1/4 WEDGE 14V .19A 1CP				
Bulb Shape	T-3 1/4	Filament	C-2F	Base Style	Wedge (T-3 1/4)
Glass Diameter (in)	0.39	MOL [†] (in)	1.06	LCL ^{††} (in)	0.56
Glass Diameter (mm)	10	MOL (mm)	26.80	LCL (mm)	14.20
Volts	14	MSCP [‡]	1	Avg Life Hrs	4000
Watts	2.66	Amps	0.19	RoHS Compliant	Yes

[†] MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

[‡] MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

^{††} LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.