





[illegible]




NOTES

1. 梱包数量: 1000個/リール  
NUMBER OF CONNECTOR: 1000PCS/REEL
2. リードテープ長さ  
LEAD TAPE LENGTH



3. トップテープの剥離強度:  $0.6 \pm 0.35N(60 \pm 35gf)$  (剥離方向は下図参照)  
PEELING OFF FORCE OF TOP TAPE:  $0.6 \pm 0.35N(60 \pm 35gf)$   
(PEELING DIRECTION IS SHOWN IN FOLLOWING FIG.)  
<剥離速度: 300mm/min (参考)>  
PEELING SPEED: 300mm/min. (REFERENCE)

4. 53398-\*\*-19 の詳細寸法については図面 SD-53398-032 を参照下さい。  
RE DETAILED DIMENSIONS, SEE SD-53398-032.
5. 材料 (MATERIAL)  
キャリアテープ (CARRIER TAPE): ポリプロピレン (POLYPROPYLENE)  
トップテープ (TOP TAPE): PET, PE, PEF  
リール (REEL): ポリスチレン (P.S.) <リサイクル材含む>  
POLYSTYRENE (P.S.) <RECYCLE MATERIAL CONTAINED>
6. 本製品は 53398-\*\*-90 の鉛フリー品である。  
THIS PRODUCT IS LEAD FREE OF 53398-\*\*-90.
7. 本製品は乾燥剤入り、ハイバリア梱包仕様である。  
THIS PRODUCT IS HIGH BARRIER PACKAGE WITH DESICCANT.



16幅テープ  
(TAPE WIDTH: 16)

|                                |      |      |             |             |             |              |            |
|--------------------------------|------|------|-------------|-------------|-------------|--------------|------------|
| 16                             | 21.4 | 17.4 | 3.7<br>2.45 | 9.5<br>8.25 | 5.8<br>4.55 | 53398-0371   | 3          |
| キャリアテープ幅<br>CARRIER TAPE WIDTH | E    | D    | (C)         | (B)         | (A)         | 53398-0271   | 2          |
|                                |      |      |             |             |             | MATERIAL NO. | 極数<br>CKT. |

|                                                                                 |             |                                                            |            |                                                                                                                                  |                   |                                                                           |                             |                              |                     |
|---------------------------------------------------------------------------------|-------------|------------------------------------------------------------|------------|----------------------------------------------------------------------------------------------------------------------------------|-------------------|---------------------------------------------------------------------------|-----------------------------|------------------------------|---------------------|
| REVISED<br>EC NO.: J2009-2060<br>DRAWN: IKON<br>CHKD: MATSUMOTO<br>APPR: NUKITA | DESCRIPTION | GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                   |            | DIMENSION STYLE<br>MM ONLY                                                                                                       |                   | SCALE<br>---                                                              | DESIGN UNITS<br>METRIC      | THIRD ANGLE<br>PROJECTION    |                     |
|                                                                                 |             | 10 UNDER                                                   | ± 0.2      | DRAWN BY<br>NINOMIYA                                                                                                             | DATE<br>'04/02/06 | TITLE<br>1.25 W/B CONN WAFER ASSY<br>FOR SMT. EMBSTP. PKG.<br>-LEAD FREE- | MOLEX<br>MOLEX INCORPORATED | DOCUMENT NO.<br>SD-53398-033 | SHEET NO.<br>1 OF 3 |
|                                                                                 |             | 10 OVER 30 UNDER                                           | ± 0.25     | CHECKED BY<br>K. TOJO                                                                                                            | DATE<br>'04/02/06 |                                                                           |                             |                              |                     |
|                                                                                 |             | 30 OVER                                                    | ± 0.3      | APPROVED BY<br>M. SASAO                                                                                                          | DATE<br>'04/02/06 |                                                                           |                             |                              |                     |
|                                                                                 |             | ANGULAR ± 3 °                                              |            | MATERIAL NO.                                                                                                                     |                   |                                                                           |                             |                              |                     |
|                                                                                 |             | DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS |            | SEE TABLE & SHEET 2.3                                                                                                            |                   |                                                                           |                             |                              |                     |
|                                                                                 |             | REV                                                        | SIZE<br>A3 | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX<br>INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                   |                                                                           |                             |                              |                     |

F

E

D

C

B

A

F


E

D

C


B

A




引き出し方向  
PULL OUT DIRECTION

24幅テープ  
(TAPE WIDTH:24)




SECT:Y-Y



引き出し方向  
PULL OUT DIRECTION



32幅テープ  
(TAPE WIDTH:32)



SECT:Y-Y

|                                |      |      |       |       |       |              |            |
|--------------------------------|------|------|-------|-------|-------|--------------|------------|
| 32                             | 37.4 | 33.4 | 16.2  | 22    | 18.3  | 53398-1371   | 13         |
|                                |      |      | 14.95 | 20.75 | 17.05 | ▲ -1271      | 12         |
| 24                             | 29.4 | 25.4 | 13.7  | 19.5  | 15.8  | ▲ -1171      | 11         |
|                                |      |      | 12.45 | 18.25 | 14.55 | ▲ -1071      | 10         |
|                                |      |      | 11.2  | 17    | 13.3  | ▲ -0971      | 9          |
|                                |      |      | 9.95  | 15.75 | 12.05 | ▲ -0871      | 8          |
|                                |      |      | 8.7   | 14.5  | 10.8  | ▲ -0771      | 7          |
|                                |      |      | 7.45  | 13.25 | 9.55  | ▲ -0671      | 6          |
|                                |      |      | 6.2   | 12    | 8.3   | ▼ -0571      | 5          |
|                                |      |      | 4.95  | 10.75 | 7.05  | 53398-0471   | 4          |
| キャリアテープ幅<br>CARRIER TAPE WIDTH | E    | D    | (C)   | (B)   | (A)   | MATERIAL NO. | 極数<br>CKT. |

|                                                                                                                       |             |                                                            |            |                                                                                                                                  |                   |                                                                           |                        |                           |  |  |  |
|-----------------------------------------------------------------------------------------------------------------------|-------------|------------------------------------------------------------|------------|----------------------------------------------------------------------------------------------------------------------------------|-------------------|---------------------------------------------------------------------------|------------------------|---------------------------|--|--|--|
| REVISED<br>EC NO: J2009-2060<br>DRWN:TKON<br>CHKD:HMATSUMOTO<br>APPR:NUKITA<br>2009/05/20<br>2009/05/21<br>2009/05/21 | DESCRIPTION | GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                   |            | DIMENSION STYLE<br>MM ONLY                                                                                                       |                   | SCALE<br>---                                                              | DESIGN UNITS<br>METRIC | THIRD ANGLE<br>PROJECTION |  |  |  |
|                                                                                                                       |             | 10 UNDER                                                   | $\pm$ 0.2  | DRAWN BY<br>NINOMIYA                                                                                                             | DATE<br>'04/02/06 | TITLE<br>1.25 W/B CONN WAFER ASSY<br>FOR SMT. EMBSTP. PKG.<br>-LEAD FREE- |                        |                           |  |  |  |
|                                                                                                                       |             | 10 OVER 30 UNDER                                           | $\pm$ 0.25 | CHECKED BY<br>K. TOJO                                                                                                            | DATE<br>'04/02/06 |                                                                           |                        |                           |  |  |  |
|                                                                                                                       |             | 30 OVER                                                    | $\pm$ 0.3  | APPROVED BY<br>M. SASAO                                                                                                          | DATE<br>'04/02/06 | MOLEX INCORPORATED                                                        |                        |                           |  |  |  |
| B                                                                                                                     | REV         | ANGULAR $\pm$ 3 °                                          |            | MATERIAL NO.<br>SEE TABLE & SHEET 1.3                                                                                            |                   | DOCUMENT NO.<br>SD-53398-033                                              |                        | SHEET NO.<br>2 OF 3       |  |  |  |
|                                                                                                                       |             | DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS |            | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX<br>INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                   |                                                                           |                        |                           |  |  |  |



44幅テープ  
(TAPE WIDTH:44)

|                 |                   |            |
|-----------------|-------------------|------------|
| REVISED         | EC NO: J2009-2060 | 2009/05/20 |
| DRWN:TKON       | 2009/05/21        |            |
| CHKD:HMATSUMOTO | 2009/05/21        |            |
| APPR:NUKITA     | 2009/05/21        |            |
| REV             | DESCRIPTION       |            |
| B               |                   |            |

| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                   |       |
|------------------------------------------------------------|-------|
| 10 UNDER                                                   | ±0.2  |
| 10 OVER 30 UNDER                                           | ±0.25 |
| 30 OVER                                                    | ±0.3  |
| ANGULAR                                                    | ±3 °  |
| DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS |       |

|                                |  |                                                                                                                                  |      |                                                                           |               |                    |                          |          |              |                     |  |
|--------------------------------|--|----------------------------------------------------------------------------------------------------------------------------------|------|---------------------------------------------------------------------------|---------------|--------------------|--------------------------|----------|--------------|---------------------|--|
| 44                             |  | 49.4                                                                                                                             | 45.4 | 18.7<br>17.45                                                             | 24.5<br>23.25 | 20.8<br>19.55      | 53398-1571<br>53398-1471 | 15<br>14 |              |                     |  |
| キャリアテープ幅<br>CARRIER TAPE WIDTH |  |                                                                                                                                  |      | E                                                                         | D             | (C)                | (B)                      | (A)      | MATERIAL NO. | 極数<br>CKT.          |  |
| DIMENSION STYLE<br>MM ONLY     |  |                                                                                                                                  |      |                                                                           | SCALE<br>---  |                    | DESIGN UNITS<br>METRIC   |          | ◎ 第三角<br>投影  |                     |  |
| DRAWN BY<br>NINOMIYA           |  | DATE<br>'04/02/06                                                                                                                |      | TITLE<br>1.25 W/B CONN WAFER ASSY<br>FOR SMT. EMBSTP. PKG.<br>-LEAD FREE- |               |                    |                          |          |              |                     |  |
| CHECKED BY<br>K. TOJO          |  | DATE<br>'04/02/06                                                                                                                |      |                                                                           |               |                    |                          |          |              |                     |  |
| APPROVED BY<br>M. SASAO        |  | DATE<br>'04/02/06                                                                                                                |      | molex                                                                     |               | MOLEX INCORPORATED |                          |          |              |                     |  |
| MATERIAL NO.                   |  | SEE TABLE & SHEET 1.2                                                                                                            |      |                                                                           |               |                    |                          |          |              |                     |  |
|                                |  |                                                                                                                                  |      | DOCUMENT NO.                                                              |               | SD-53398-033       |                          |          |              | SHEET NO.<br>3 OF 3 |  |
| SIZE<br>A3                     |  | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX<br>INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |      |                                                                           |               |                    |                          |          |              |                     |  |