

LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	ECR-05-016219	26NOV05	JMS	FWK

NOTES:

- 1

PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2

100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3

Ag PLATING
- 4

ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:DC – 2 GHz

NOMINAL IMPEDANCE:75 Ohm

INSULATION RESISTANCE:5000 MOhm

WORKING VOLTAGE:500 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE:1500 Volts RMS Max

CONTACT RESISTANCE:

CENTRE CONTACT:1.50 mOhm Max

OUTER CONTACT:0.20 mOhm Max

VSWR @ xGHz:N/A

INSERTION LOSS xdb:N/A
- 5

MECHANICAL CHARATERISTICS



COUPLING RETENTION FORCE:N/A

CABLE RETENETION FORCE:N/A

DURABILITY:500 Cycles Min
- 6

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:-65 to +165 DegC



		1	1	BRASS	3	SLEEVE	5
		1	1	PTFE		INSULATION	4
		1	1	BRASS	3	CONTACT	3
		1	1	PTFE		INSULATION	2
		1	1	BRASS	3	BODY	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		3	3				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J.SANDWELL	26NOV05	tyco Tyco Electronics Corporation Electronics Bideford EX39 4HE		
		CHK	S.PARLOW	26NOV05			
		APVD	F.WHEELER-KING	26NOV05	NAME BNC PANEL SOCKET 50 OHM & 75 OHM		
		PRODUCT SPEC 108-3435					
		APPLICATION SPEC					
		WEIGHT			SIZE	CAGE CODE	RESTRICTED TO
		—			A3	00779	—
		CUSTOMER DRAWING			SCALE	SHEET	REV
					NTS	1 OF 1	C