

Straight Blade Devices  
**15 and 20 Ampere, 250 Volts**  
 2 Pole, 3 Wire Grounding

**Insulgrip® and Valise® Connector Bodies and Flanged Receptacles**



**NEMA 6-15R**  
15A 250V  
UL CSA



**NEMA 6-20R**  
20A 250V  
UL Listed

## Connector Bodies

### Insulgrip®

Description	Cord Diameter	Catalog Numbers	
Insulgrip® Connector Body, black and white nylon, multiple drive screws.	.230"-.720" (5.8-18.3)	<b>HBL5669C</b>	<b>HBL5469C</b>
Valise® Connector Body, yellow nylon.	.220"-.660" (5.6-16.8)	<b>HBL5669VY</b>	<b>HBL5469VY</b>

Note: See page A-45 for accessories.



**HBL5669C**



**HBL5669VY**



**HBL5679C**



**HBL5656**

## Flanged Receptacles

Description	Catalog Numbers	
Nylon casing, multiple drive screws.	<b>HBL5679C</b>	<b>HBL5479C</b>
Stainless steel flange, brown phenolic housing (mounting screws packaged separately).	<b>HBL5656</b>	-

Notes: Connector bodies are not HP rated.

\*Watertight connectors IP55 suitability when closure plug inserted or when installed and used properly with mating Elastogrip watertight plug.

See page A-45 for accessories.