

| PART NAME | UTILIBOX (STYLE E) | PART No. | CU-789-MB TD CU-792-MB |
|-----------|--------------------|----------|------------------------|
|-----------|--------------------|----------|------------------------|

**MATERIAL:**  
ABS THERMOPLASTIC  
FLAMMABILITY RATING OF 94V-0 AT  
0.070" THICKNESS AND CONTINUOUS  
USE TEMPERATURE OF 70° C.)

**COLOR:** BLACK


**FINISH:**  
BODY - OUTSIDE SURFACES ARE TEXTURED FINISH  
WITH TEXTURED INSERT AREA.  
COVER - SURFACES ARE SMOOTH.  
  
**NOTE:** ALL DIMENSIONS HAVE  $\pm 0.010$  TOLERANCE  
UNLESS OTHERWISE SPECIFIED.

MOUNTING BOSSES USE EITHER M2.5 METRIC  
OR #4 STD. SHEET METAL SCREWS  $\times 0.250"$  LG.  
(NOT SUPPLIED)

COVER REDUCES INSIDE HEIGHT BY 0.075.

LENGTH AND WIDTH DIMENSIONS ARE  
TAKEN FROM CLOSED END OF THE BOX.  
DIMENSIONS INCREASE SLIGHTLY AT  
OPEN END DUE TO TAPER.

FOUR (4) #4  $\times 0.500"$  LG. SELF THREADING  
SCREWS WITH HI/LOW THREADS  
ARE SUPPLIED FOR MOUNTING COVER.



| PART No.  | A     | B     | C     | D     | E     | F     | G     | H     | J     | K     | L     | M     | N     | P     | Q     | R     | S     | T     |
|-----------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| CU-789-MB | 3.000 | 2.000 | 0.900 | 2.047 | 3.875 | 2.468 | 1.234 | 1.468 | 0.734 | 2.790 | 1.781 | 3.500 | 1.039 | 2.968 | 1.968 | 1.750 | 0.984 | 0.609 |
| CU-790-MB | 3.000 | 2.000 | 1.500 | 2.079 | 3.875 | 2.468 | 1.234 | 1.468 | 0.734 | 2.790 | 1.781 | 3.500 | 1.039 | 3.000 | 2.000 | 1.750 | 1.000 | 0.625 |
| CU-791-MB | 3.000 | 3.000 | 1.500 | 3.079 | 3.875 | 2.468 | 1.234 | 2.468 | 1.234 | 2.790 | 2.781 | 3.500 | 1.539 | 3.000 | 3.000 | 1.750 | 1.500 | 0.625 |
| CU-792-MB | 4.000 | 1.750 | 1.000 | 1.802 | 4.875 | 3.468 | 1.734 | 1.218 | 0.609 | 3.790 | 1.531 | 4.500 | 0.901 | 3.978 | 1.733 | 3.000 | 0.866 | 0.489 |