

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0732045213
Status: Active
Overview: TNC RF Connectors
Description: 50 Ohms, TNC Right-Angle, PCB, Jack Receptacle, Body Nickel Plated Brass

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family RF/Coax Connectors
Series 73204
Overview TNC RF Connectors
Product Name TNC
Style PCB
UPC 800753691575
Wire/Cable Type N/A


Physical
Cable Attachment N/A
Gender Jack
Keying to Mating Part None
Net Weight 15.797/g
Orientation Right Angle
PCB Mounting Through Hole
PCB Thickness - Recommended 2.40mm
Packaging Type Tray
Panel Mount No
Panel Mount Method N/A

Electrical
Impedance 50#

Solder Process Data
Duration at Max. Process Temperature (seconds) 010
Lead-freeProcess Capability SMC&WAVE
Max. Cycles at Max. Process Temperature 002
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers
Product Specification RPS-73204-002
Sales Drawing SD-73204-5213, SD-73216-273



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant with Exemption 6(c) REACH SVHC Contains SVHC(2015 June 15): No Halogen-Free Status Low-Halogen Need more information on product environmental compliance? Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	China RoHS China ROHS 50 Image ELV Not Relevant
--	--

Search Parts in this Series
73204 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION