



Bud Industries, Inc.

# QUALITY ENCLOSURES

Accessories - Power Outlet  
Strips

## Power Outlet Strip

### ***Design Features***

Power outlet strips can be used in cabinets, on walls or along work or test benches. Silver gray housings; no loose wires can come into contact with conductor wires. Strips snap into adjustable mounting clips. Grounding type 15 amp., 125 volt receptacles, 15 amp thermal-type circuit breaker with reset. 14 gauge, 3 wire, 6 foot power cord. All components U. L. approved.



| Power Outlet Strips |  |                |        |            |
|---------------------|--|----------------|--------|------------|
| Catalog Number      |  | No. of Outlets | Length | Weight Lbs |
| POS-4               |  | 4              | 17.50" | 2.00       |
| POS-6               |  | 6              | 12.25" | 1.75       |
| POS-7               |  | 7              | 48.00" | 3.50       |
| POS-9               |  | 9              | 60.00" | 4.25       |
| POS-11              |  | 11             | 72.00" | 4.75       |

PART  
NAME

## POWER OUTLET STRIP

PART  
No.

POS-4-S TO POS-66

14 GAUGE 3 WIRE POWER CORD  
6 FOOT LONGMOLDED ON 3-PRONG PLUG  
15 AMP 125 VOLT

STRAIN RELIEF

GROUNDING TYPE 15 AMP 125 VOLT  
RECEPTACLE

1.062

1.062

H

SURGE PROTECTION  
INDICATOR LAMP  
15 AMP 125 VOLT

D TYP.

C

B

CIRCUIT BREAKER THERMAL TYPE  
15 AMP 125 VOLT  
WITH RESETILLUMINATED  
ON/ OFF SWITCH  
15 AMP 125 VOLT


0.188

HOUSING

F

0.125

A

MATERIAL:HOUSING (TOP & BOTTOM CHANNELS) &  
MTG. CLIPS - ALUMINUM EXTRUSIONS  
END CAPS - ABS PLASTICFINISH:HOUSING - GREY  
- PUTTY WHITE (POS-66 ONLY)  
RECEPTACLES, POWER CORD & END  
CAPS - BLACK  
- PUTTY WHITE (POS-66 ONLY)  
MTG. CLIPS - NATURAL

| PART NO. | QTY. OF<br>OUTLETS | SURGE<br>SUPPRESSED | A      | B     | C                            | D     | E     | F     | G     | H     | QTY. OF<br>MTG. CLIPS |
|----------|--------------------|---------------------|--------|-------|------------------------------|-------|-------|-------|-------|-------|-----------------------|
| POS-4-S  | (4)                | YES                 | 17.625 | 0.938 | (3) SPACES @ 3.062 = 9.188   | 3.062 | 2.000 | 1.750 | 2.093 | 2.000 | (2)                   |
| POS-6    | (6)                | NO                  | 12.250 | 0.969 | (5) SPACES @ 1.250 = 6.250   | 1.250 | 1.828 | 1.563 | 1.843 | 1.750 | (2)                   |
| POS-7-S  | (7)                | YES                 | 48.125 | 4.625 | (6) SPACES @ 6.000 = 36.000  | 6.000 | 2.000 | 1.750 | 2.093 | 2.000 | (2)                   |
| POS-9-S  | (9)                | YES                 | 60.125 | 4.625 | (8) SPACES @ 6.000 = 48.000  | 6.000 | 2.000 | 1.750 | 2.093 | 2.000 | (3)                   |
| POS-11-S | (11)               | YES                 | 72.125 | 4.625 | (10) SPACES @ 6.000 = 60.000 | 6.000 | 2.000 | 1.750 | 2.093 | 2.000 | (3)                   |
| POS-66   | (6)                | YES                 | 13.000 | 0.969 | (5) SPACES @ 1.250 = 6.250   | 1.250 | 2.000 | 1.750 | 2.093 | 2.000 | (2)                   |