

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1040790300](#)
Status: **Active**
Description: 1.50mm Wire-to-Board Power Header Connector, 3 Circuits

Documents:

[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-104080-001 \(PDF\)](#)
[Packaging Specification PK-104079-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Crimp Housings
Series [104079](#)
Application Power, Signal, Wire-to-Board
Product Name IllumiMate™

Physical

Circuits (maximum) 3
Color - Resin Natural
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin High Temperature Thermoplastic
Number of Rows 1
Packaging Type N/A
Panel Mount No
Pitch - Mating Interface 1.50mm
Polarized to Mating Part Yes
Temperature Range - Operating -25°C to +130°C


Electrical

Current - Maximum per Contact 1A

Material Info

Reference - Drawing Numbers

[Packaging Specification](#) PK-104079-001
[Product Specification](#) PS-104080-001
[Sales Drawing](#) SD-104079-001



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[104079Series](#)

Mates With
[1040800310](#)