




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



ADHESIVE BACKING:
PRESSURE SENSITIVE FOAM 0.04 (1.0) THICK
WITH PROTECTIVE LINER. LINER TO EXTEND
BEYOND EDGE TO FORM RELEASE TAB.




OPEN VIEW

PANDUIT PART NO. *	DIMENSIONS			WEIGHT lbs (grams) / 100 pcs
	"A"	"B"	"C"	
LC10-A---	1.00 (25.4)	1.51 (38.35)	0.84 (21.34)	1.02 (463)

- NOTES:
- * 1. SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.
 - 2. PART TO BE INSTALLED ON A CLEAN, DRY, SMOOTH GREASE FREE SURFACE.
 - 3. TO APPLY PART:
 - (A) REMOVE PROTECTIVE LINER.
 - (B) PLACE PART IN DESIRED LOCATION.
 - (C) APPLY PRESSURE TO FLAT SURFACE OF PART.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

A								TITLE				A
								LATCHING CLIP - (LC10-A-__)				
								CUSTOMER DRAWING				
								ITEM REVISION NAME		10B015JI/00		
								DATASET FILE NAME				
								10B015JI_DC/00 - GB0239GQ_REV01		MATERIAL: RIGID PVC		
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				
								.X ± .xxx ± 0.01 [.25] .XX ± 0.03 [.8] ANGLES ± 2 °				
	1	4/24/13	BWG	KJM	RTFI	REDRAWN NEW CAD FILE CREATED. SEE ECN FOR FULL DESCRIPTION.	GB0239GQ/01			THIRD ANGLE PROJECTION	DRAWING NUMBER: GB0239GQ	
	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	