



Terminal blocks

to Type 266

Type 262 page 102

Accessories

for Type 266

Coding set
700024 page 206

Type 266

Header, centerline 7.62 mm / 0.300 inches, horizontal mounting, squarecontact pins 1 mm / 0.039 inches, closed ends, codable

Technical Data



300 / 15



500 V / 6 kV / 10 A

Insulation co-ordination according to EN 60664-1

Clearance and creepage distances min. 6.6 mm

Insulating material class CTI 600

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 500 1250 1250

Rated test voltage 4 8 6

Protection category according to IEC 529 IP00

Solder pin dimension 1.0 x 1.0 mm

Recommended pc board hole dia. Ø 1.5 mm


Solder pin length 3.45 mm

Pole size 2 - 12

Color black

Dimensions in mm

1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 7.62 \text{ mm} / 0.300 \text{ inches}$

Part numbers (P/N)

(information: page 110)

Complete the part number by adding the pole size.

Type 266

centerline 7.62 mm / 0.300 inches

P/N 312661



	02	03	04	05	06	07	08
09	10	11	12				

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.