

DESCRIPTION	8 and 11 Pin Square Base Sockets	
ELECTRICAL RATING	• 300 Volts, 10 Amps • 150 Volts, 15 Amps	
CONSTRUCTION	Contacts • Brass, Nickel Plated Screws • Binder Head, 6 - 32 x 1/4" Steel, Zinc Plated • Pressure Clamp, 6 - 32 x 5/16" Steel, Zinc Plated, Wire Range #12 - #22 Solid or Stranded Molding • Break Resistant Thermoplastic	
AGENCY APPROVALS	• UL recognized, File No. E60008 • CSA certified, File No. LR29513 • CE	



ORDERING CODE

PART NO.	DESCRIPTION	TERMINAL TYPE
SS08	DPDT, 8 Pin Square	Binder Head Screws
SS08-PC	DPDT, 8 Pin Square	Pressure Clamp Screws
SS11	3PDT, 11 Pin Square	Binder Head Screws
SS11-PC	3PDT, 11 Pin Square	Pressure Clamp Screws

ACCESSORIES


PART NO.	DESCRIPTION (Refer to the accessories pages 25-27)
HDB-8	Hold Down Spring

SS SERIES


RELAY SOCKETS



CUSTOM CONNECTOR



TERMINAL LOCATION



TOP VIEW

SS SERIES NOTE:

Terminals 2, 5 and 8 omitted on DPDT, 8 Pin models