


DO NOT SCALE
DIMENSIONS IN mm




METRIC

THIRD ANGLE
PROJECTION



NOTES:

- 1 PARTS PACKAGED UNASSEMBLED
- 2 BULKPAGE CONSIST OF 50 KITS
- 3 FOR MOUNTING INSTRUCTIONS SEE 114-19039
- 4 SUITABLE FOR 30-26 AWG (0,25-0,40 mm DIA) WITH 1,0 MM DIA MAX INSULATION
- 5 SUITABLE FOR 26-24 AWG (0,40-0,50 mm DIA) WITH 1,0 MM DIA MAX INSULATION
- 6 MATERIAL:
CONTACT: PHOSPHORBRONZE
HOUSING: LIQUID CRYSTAL POLYMER
PLATE: GLASSFILLED POLYESTER
COVERS: GLASSFILLED POLYESTER (BLACK)
FERRULE: TINPLATED PHOSPHORBRONZE
- 7 FINISH CONTACTS:
0,8µm AU over 1,3µm Ni IN CONTACT AREA
REMAINDER 2,0µm MAX. TIN-LEAD OVER 1,3µm Ni
- 8 MAXIMUM OUTER CABLE DIAMETER
WHEN NOT EXCEEDING COVER LID: 6,5 mm
OTHERWISE: 8,5
- 9 3D DRAWING DOESN'T SHOW FULL DETAILS



26-24 AWG CABLE CONNECTOR KIT				2/5	1-352168-2
30-26 AWG CABLE CONNECTOR KIT				2/4	1-352168-1
DESCRIPTION				NOTES	PARTNUMBER
-				CUSTOMER DRAWING	FOR REFERENCE ONLY WILL NOT BE UPDATED
-				© COPYRIGHT 1996 BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.	
-				THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION	
B	EH-0839-01	MVE	MVE	26 JUL '01	AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.
A	EH-1252-00	RB	WH	10-NOV-00	
O	EH-1111-96	DT	KK	26-SEP-96	
LTR.	REVISION RECORD	DR.	CHK.	DATE	NAME
DR.: K.KOCAKOGLU				CHK.: K.KOCAKOGLU	Z-PACK 2mm HM KIT
DATE: 26-SEP-96				DATE: 26-SEP-96	
APP.: K.KOCAKOGLU				DATE: -	20 POS. LF UNSHIELDED CABLE CONNECTOR
DWG.No.				C-352168	
REV.LTR.				B	SHEET 1 OF 1
A3					