


Pin Header 3,00 mm

Series

437




Rated current	5,0 A
Rated voltage	250 V _{RMS} / V _{DC}
Withstand voltage	1500 V _{RMS} for one minute
Material contact	Copper alloy
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-25°C to +105°C
Max. processing temper.	260°C for 10 seconds

All dimensions in mm.


pitch	3,00
termination	
contact size	□ 0,64
max. pincount	024

Product group
3


Variation




1




2



3



4



5

Positioning peg:
0 = Without peg
(for variation 2 and 4)
1 = With peg
(for variation 1, 3 and 5)

Plating:
T = Sn






Variation (1,2,3,4,5)

No. of contacts

Positioning peg (0,1)

Plating contact

PCB Layout



www.mpe-connector.de

Order code:

437-?-?-?-?-T-KS0

Mating series
see page

433
6-13