

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0464361147](#)
Status: **Active**
Overview: [EXTreme Ten60Power High-Current Connector](#)
Description: 11.00mm Pitch EXTreme Ten60Power Right-Angle Receptacle with Guides, 4 DC Power Circuits

Documents:

Drawing (PDF)	Test Summary 464361000-TS-000 (PDF)
Product Specification PS-46436-100-001 (PDF)	Datasheet (PDF)
Packaging Specification PK-46436-001-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179


General

Product Family	PCB Receptacles
Series	46436
Application	Board-to-Board, Power
Comments	See PS-46436-100 for details
Overview	EXTreme Ten60Power High-Current Connector
Product Name	EXTreme Ten60Power
UPC	884982481077

Physical

(p)ower-(s)ignal Configuration	4p - 0s
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	200
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	16.823/g
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.58mm
Packaging Type	Tray
Pitch - Mating Interface	11.00mm
Plating min - Mating	0.127µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[46436](#) Series

Mates With

[464371147](#) EXTreme Ten60Power Plug
Assembly

Current - Maximum per Contact	2.5A, 55.0A
Grounding to PCB	No
Voltage - Maximum	600V AC / 250V DC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-46436-001-000
Product Specification	PS-46436-100-001
Sales Drawing	SD-46436-1147
Test Summary	464361000-TS-000

This document was generated on 08/18/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION