



TW-20-03-L-Q-400-085

TW-08-09-F-T-165-100

TW-16-06-T-D-500-100

TW SERIES

THROUGH-HOLE BOARD STACKERS

Choice of one through six rows

TW

NO. PINS PER ROW

LEAD STYLE

PLATING OPTION

ROW OPTION

STACKER HEIGHT

TAIL SPEC

02 thru 50

Specify LEAD STYLE from chart below.

-F
= Gold flash on post, Matte Tin on tail

-L
= 10μ" (0,25 μm) Gold on post, Matte Tin on tail

-T
= Matte Tin

-S
= Single Row

-D
= Double Row

-T
= Triple Row

-Q
= Four Row

-5
= Five Row

-6
= Six Row

-“XXX”
= Stacker Height in inches (0,13 mm) .005" increments
Example: -250 = (6,35 mm) .250"

-“XXX”
= Tail Length in inches (0,13 mm) .005" increments
Example: -150 = (3,81 mm) .150"

-“XXX”
= Polarized Position (Specify position to be removed)

LEAD STYLE	OAL
-01	(8,20) .323
-02	(9,60) .377
-03	(13,60) .535
-04	(14,10) .555
-05	(15,10) .594
-06	(17,10) .673
-07	(19,10) .751
-08	(21,10) .830
-09	(11,60) .456
-10	(15,60) .614
-11	(10,08) .397
-12	(28,19) 1.110

* Style -08 & -12 = S & D only

* -D with stacker height greater than (4,06 mm) .160" will not have standoffs.

ROW OPTION	STACKER HEIGHT
-S, -D*, & -Q	(3,05) .120 MIN
-T, -5, -6	(4,06) .160 MIN

*-D with stacker height greater than (4,06 mm) .160" will not have standoffs.