



Model 5512 Adapter Kit With BNC (Male) Resistor Terminal



MATERIALS:

Body: Brass, Center Contact: Gold plated brass,
Outer Contact: Tarnish Resistant gold plated Beryllium Copper
Dielectric: Teflon
Gasket/Seals: Silicone rubber
Resistor: Deposited carbon film
Marking: "Pomona 3840-*"
Label: "TERM, *Ω 1/2W"

RATINGS:

Frequency Range: DC to 500 MHz
Resistance Tolerance: $\pm 1\%$
Power: 1/2W @ 70°C Max

ORDERING INFORMATION: Model 5512

Kit contains 1 each Model 3480-50, -75, -93, -100, -600 Ohms
Ordering Example: 5512

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA