



Product Data Sheet

Part No. WST-0905S Washable Type

DIMENSIONS



UNIT : mm
TOLERANCE : ±0.3
HOUSING MATERIAL : PBT

Type	Unit	
Rated Voltage	(V)	5
Operating Voltage	(V)	4~6
Current Consumption	(mA)	MAX.30
Sound Output (Min)	(dB)	83
Resonance Frequency	(Hz)	2730
Operating Temp	(C)	-20~+60
Storage Temp	(C)	-30~+70
Weight	(g)	1
Terminal		PIN TYPE
Dimension	mm	9.6 x H5
*Value applying at rated voltage.		
*distance for measurement 30cm		

CHARACTERISTICS

