

THA-430 Lever Handle



Characteristic

A stainless steel made handle with excellent corrosion-resistance.

Application

Thermostatic chambers / Refrigerators / Small doors for other various types of sealed storages

Operational Instruction

Tighten until proper position is attained.

Specification



Model No.	Type	Net Weight (g)	Code No.
THA-430-1R	Right	528	13001
THA-430-1L	Left	528	13002
THA-430-2R	Right	298	13003
THA-430-2L	Left	298	13004
THA-430-3R	Right	230	13005
THA-430-3L	Left	230	13006
THA-430-4R	Right	166	13007
THA-430-4L	Left	166	13008
THA-430-5R	Right	139	13009
THA-430-5L	Left	139	13010

Parts List

No.	Part Name	Material	Finish	Quantity
1	Handle	SCS13	Buffing	1
2	Base			1
3	Rivet	SUS304	—	1
4	Washer			1
5	Plate Spring			1
6	Wave Washer	SUS	—	1
7	Keeper	SCS13	Buffing	1

※ Instead of No.5, a wave washer is used for THA-430-3 to 5.

※ No.6 is not used for THA-430-3 to 5.



The figure shows for right side. The shape of left side is symmetrical to right side.

Size List

Model No.	(A)	(B)	C	D	E	F	G	H	J	K	(L)	(N)	P	(Q)	S	(T)
THA-430-1R	170	127	45	34	90	70	40	28	52	40	48.6	17.6	6	19	14	43
THA-430-1L																
THA-430-2R	140	111.4	40	25	80	52	35	24		34	43.6	14.6	5	17		34
THA-430-2L									50						12	
THA-430-3R	125	98.5	32	22	65	43	32	23		35		14.2	5	18		30
THA-430-3L											35.2					
THA-430-4R	110	83	30	20	60	40						13.2	5	14.5	10	28
THA-430-4L							30	20	45	32						
THA-430-5R	90	68		17	55	37					27.1	12.6				
THA-430-5L																