

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300390236](#)
Status: **Active**
Overview: [Brad Mini-Change Connectors](#)
Description: Micro-Change (M12) Receptacle to DeviceNet D-Net Open with Screws, 5 Poles, Male (Straight) to Female (Straight), 5 Poles, PVC Cable, 5.0m (16.40') Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR6837


General
Product Family Industrial Cordsets
Series [130039](#)
Connector End A Micro-Change (M12)
Connector End B D-Net Open
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Mini-Change Connectors](#)
Product Name DeviceNet, Micro-Change (M12)
Region Europe
Type Double Ended
UPC 78678887213

Physical
Cable Diameter N/A
Cable Length 5.0m (16.40')
Color - Cable Jacket Gray
Coupling Style Threaded
Gender Female-Male
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Coupling Nut N/A
Material - Plating Mating Gold
Orientation Straight to Straight
Poles 5
Temperature Range - Operating -20°C to +80°C
Wire Size AWG 22
Wire/Cable Type E152210

Electrical
Current - Maximum per Contact 4.0A
Voltage - Maximum 250V AC

Material Info
Engineering Number DNDC304-M050

Reference - Drawing Numbers
Sales Drawing SD-130039-029



EU ELV
Not Reviewed

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130039](#) Series