


Twist-Lock® Devices

30 Ampere, 3Ø Y 120/208, 277/480 and 347/600 Volts AC

4 Pole, 5 Wire Grounding

Insulgrip® Plugs and Flanged Inlets


30A 3ØY
120/208V AC
 NEMA L21-30P
 UL/CSA
 3 HP



30A 3ØY
277/480V AC
 NEMA L22-30P
 UL/CSA
 10 HP



30A 3ØY
347/600V AC
 NEMA L23-30P
 UL/CSA

**HBL2811SW****HBL2811S****HBL2811****HBL2815SW****HBL2815****Plugs****Watertight Safety-Shroud®****IP66** SUITABILITY

Description	Cord Dia.	Catalog Numbers		
Black Valox® housing, white Valox® clamps.	.35"-1.15" (9-29)	HBL2811SW	-	-

Safety-Shroud**IP20** SUITABILITY

Description	Cord Dia.	Catalog Numbers		
Black and white nylon body, white Valox® shroud. Can be used with the Insulgrip Connector Bodies.	.35"-1.15" (9-29)	HBL2811S	-	-

Accessories on page B-40.

Insulgrip**IP20** SUITABILITY

Description	Cord Dia.	Catalog Numbers		
Black and white nylon.	.35"-1.15" (9-29)	HBL2811	HBL2821	HBL2831
Corrosion resistant, yellow nylon.	.35"-1.15" (9-29)	HBL28CM11	-	-
Black and white for flat cable.	.35"-1.15" (9-29)	HBL2811FC	-	-
All black nylon.	.35"-1.15" (9-29)	HBL2811BK	-	-

Accessories on page B-53.

Flanged Inlets**Watertight Safety-Shroud****IP66** SUITABILITY

Description	Catalog Numbers		
Gray Valox® housing and flange.	HBL2815SW	-	-

Accessories on page B-54.

Insulgrip**IP20** SUITABILITY

Description	Catalog Numbers		
Nylon casing, back wired.	HBL2815	HBL2825	HBL2835

Accessories on page B-52.

Notes: For technical information on Twist-Lock® and Watertight Safety-Shroud Devices see pages B-69 and 70.

HBLMITL - For use with Watertight Safety-Shroud receptacles, see page B-39.



Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.