

パワートランジスタ

POWER TRANSISTORS

SHINDENGEN ELECTRIC MFG 32E D 8219387 0000018 0 SHEJ

高耐圧・超高速スイッチングトランジスタ High Voltage・Ultra High Speed Switching Transistors

F3 series

T-35-19

品 名		絶 对 最 大 定 格 Absolute Maximum Ratings									電 氣 の ・ 熱 の 特 性 Electrical Characteristics									外 形 No. Outline No.
EIAJ No.	Type No.	V _{CB0} [V]	V _{CE0} [V]	V _{EB0} [V]	I _C [A]	I _B [A]	P _T [W]	T _{stg} [°C]	T _J [°C]	V _{CE0} (sus) (min) [V]	hFE (min)	V _{CE} (sat) (max) [V]	V _{BE} (sat) (max) [V]	θ _{JA} (max) [°C/W]	f _T (std) [MHz]	t _{on} (max) [μS]	t _s (max) [μS]	t _f (max) [μS]		
2SC3219	T6V20F3	230	230	7	6	2	50	-55~+150	+150	200	10	1	1.5	2.5	20	0.3	0.5	0.1	Fig. 1	
3220	T10W20F3				10	4	80							1.56					Fig. 3	
3221	T6M20F3				6	2	80							1.56					Fig. 4	
3222	T10M20F3				10	4	100							1.25					Fig. 5	
3223	T20M20F3				20	7	200							0.62					Fig. 6	
3162	T3V40F3	500	400	7	3	1	40	-55~+150	+150	400	10	1	1.5	3.13	20	0.3	1	0.1	Fig. 1	
3163	T6V40F3				6	2	50							2.5					Fig. 3	
3164	T10W40F3				10	4	100							1.25					Fig. 4	
3165	T3M40F3				3	1	60							2.08					Fig. 5	
3166	T6M40F3				6	2	80							1.56					Fig. 6	
3167	T10M40F3				10	4	100							1.25					Fig. 5	
3168	T20M40F3				20	7	200							0.63					Fig. 6	

高耐圧・高速スイッチングトランジスタ High Voltage・High Speed Switching Transistors

FX series

品 名		絶 对 最 大 定 格 Absolute Maximum Ratings									電 気 的 ・ 熱 的 特 性 Electrical Characteristics									外 形 No. Outline No.
EIAJ No.	Type No.	V _{CB0} [V]	V _{CE0} [V]	V _{EB0} [V]	I _C [A]	I _B [A]	P _T [W]	T _{stg} [°C]	T _J [°C]	V _{CE0} (sus) (min) [V]	h _{FE} (min)	V _{CE} (sat) (max) [V]	V _{BE} (sat) (max) [V]	θ _{JO} (max) [°C/W]	f _T (std) [MHz]	t _{ON} (max) [μS]	t _S (max) [μS]	t _F (max) [μS]		
2SC4051	T3V45FX	600	450	7	3	1	40	-55~+150	+150	450	10	1	1.5	3.12	20	0.5	2	0.2	Fig. 1	
4052	TP3V45FX				3	1	25							5					Fig. 2	
4053	T5V45FX				5	2	50							2.5					Fig. 1	
4054	TP5V45FX				5	2	30							4.16					Fig. 2	
4055	T8V45FX				8	4	60							2.08					Fig. 1	
4056	TP8V45FX				8	4	45							2.77					Fig. 2	
4057	T8W45FX				8	4	80							1.56					Fig. 3	
4058	T10W45FX				10	4	100							1.25						
4059	T15W45FX				15	6	130							0.96						
4060	T20W45FX				20	7	150							0.83						
3714	T20W40FX	500	400		20	7	200			400			0.625					0.3	Fig. 10	

外形図 Outline Dimensions

[Unit: mm]

Fig. 1




Fig. 2




Fig. 3

