



RMQ Titan

Complete Units for Cover Mounting

						Front ring titanium		
		Button plate	Color	Contacts N.O. = normally open N.C. = normally closed ⊕ = Positive opening safety function to IEC/EN 60 947-5-1 N.O. N.C.		Type Article No.	Price see price list	
Pushbuttons, IP67, IP69K								
	Flush	START	green	1	–		M22-D-G-GB1/K10 109420	
		STOP	red	–	1 ⊕		M22-D-R-GB0/K01 109421	
		START	green	1	1 ⊕		M22-D-G-GB1/K11 109422	
		STOP	red	1	1 ⊕		M22-D-R-GB0/K11 109423	
	Extended	START	green	1	–		M22-DH-G-GB1/K10 109424	
		STOP	red	–	1 ⊕		M22-DH-R-GB0/K01 109425	
		START	green	1	1 ⊕		M22-DH-G-GB1/K11 109426	
		STOP	red	1	1 ⊕		M22-DH-R-GB0/K11 109427	
	Mushroom-head	START	green	1	–		M22-DP-G-GB1/K10 109428	
		STOP	red	–	1 ⊕		M22-DP-R-GB0/K01 109429	
		START	green	1	1 ⊕		M22-DP-G-GB1/K11 109430	
		STOP	red	1	1 ⊕		M22-DP-R-GB0/K11 109431	
Double pushbuttons, IP66								
	Cover plate, white	START	green	1	–		M22-DDL-GR-GB1/GB0/K11 109432	
		STOP	red	–	1 ⊕			
With LED element lens white 85 – 264 V AC		START	green	1	–		M22-DDL-GR-GB1/GB0/K11/230-W 109433	
		STOP	red	–	1 ⊕			
Selector switches, black thumb-grip handle, IP66								
Maintained/spring-return function can be changed using M22-XC-Y coding adapters								
	Two position, maintained		1	–			M22-WKV/K10 109434	
			1	1 ⊕			M22-WKV/K11 109435	
Three position, maintained			2	–		 	M22-WRK3/K20 216520	

Notes




¹⁾ Switch positions 0, I, II correspond to the position of the selector switch viewed from the front.

RMQ Titan

Complete Units for Cover Mounting

NEMA/UL/CSA 12, 13, 3R, 4X / CE

Pushbuttons and Stacklights

				Front ring titanium	
Button plate	Color	Contacts N.O. = normally open N.C. = normally closed ⊕ = Positive opening safety function to IEC/EN 60 947-5-1 N.O. N.C.		Type Article No.	Price see price list
Key-operated selector switches, with 1 key, IP66 Maintained/spring-return function and key withdrawability can be changed using M22-XC-... coding adapters					
Two position, maintained MS1 lock mechanism 		–	1 ⊕		M22-WRS/K01 109436
		1	1 ⊕		M22-WRS/K11 216517
Three position, maintained MS1 lock mechanism		2	–		M22-WRS3/K20 109437
Indicating lights, IP 67, 69K					
Flush lens, with LED element 85 – 264 V AC		green			M22-L-G/230-G 109438
		red			M22-L-R/230-R 109439
		yellow			M22-L-Y/230-W 109440
		white			M22-L-W/230-W 109441
		blue			M22-L-B/230-B 109442
Flush lens, with LED element 12 – 30 V AC/DC		green			M22-L-G/G 109443
		red			M22-L-R/R 109444
		yellow			M22-L-Y/W 109445
		white			M22-L-W/W 109446
		blue			M22-L-B/B 109579
Extended lens, with LED element 85 – 264 V AC		green			M22-LH-G/230-G 109447
		red			M22-LH-R/230-R 109448
		yellow			M22-LH-Y/230-W 109449
		white			M22-LH-W/230-W 109450
		blue			M22-LH-B/230-B 109451
Extended lens, with LED element 12 – 30 V AC/DC		green			M22-LH-G/G 109452
		red			M22-LH-R/R 109453
		yellow			M22-LH-Y/W 109454
		white			M22-LH-W/W 109455
		blue			M22-LH-B/B 109456

RMQ Titan
 Complete Units for Cover Mounting

					Front ring titanium	
Button plate Color		Contacts N.O. = normally open N.C. = normally closed ⊕ = Positive opening safety function to IEC/EN 60 947-5-1 N.O. N.C.		Type Article No.	Price see price list	
Illuminated pushbuttons, IP 67, 69K						
Flush lens, with LED element 85 – 264 V AC		green	1	1 ⊕		M22-DL-G/K11/230-G 109457
		red				M22-DL-R/K11/230-R 109458
		yellow				M22-DL-Y/K11/230-W 109459
		white				M22-DL-W/K11/230-W 109460
		blue				M22-DL-B/K11/230-B 109461
Flush lens, with LED element 12 – 30 V AC/DC		green			M22-DL-G/K11/G 109462	
		red			M22-DL-R/K11/R 109463	
		yellow			M22-DL-Y/K11/W 109464	
		white			M22-DL-W/K11/W 109465	
		blue			M22-DL-B/K11/B 109466	
Extended lens, with LED element 85 – 264 V AC		green			M22-DLH-G/K11/230-G 109467	
		red			M22-DLH-R/K11/230-R 109468	
		yellow			M22-DLH-Y/K11/230-W 109469	
		white			M22-DLH-W/K11/230-W 109470	
		blue			M22-DLH-B/K11/230-B 109471	
Extended lens, with LED element 12 – 30 V AC/DC		green			M22-DLH-G/K11/G 109472	
		red			M22-DLH-R/K11/R 109473	
		yellow			M22-DLH-Y/K11/W 109474	
		white			M22-DLH-W/K11/W 109475	
		blue			M22-DLH-B/K11/B 109476	