

# PDMM-20 Pocket Multimeter

## Don't let the size fool you!



### Conveniently fits into any pocket.

Take an inventory of the items in your pocket - pen, pencil, non-contact voltage detector, and PDMM-20 pocket multimeter. Greenlee's PDMM-20 pocket multimeter is so compact and lightweight that you won't even notice it in your pocket. What you will notice is the tremendous amount of features that have been designed into this unique multimeter! The PDMM-20 is an auto-function, low impedance multimeter. Auto-function means that you do not have to switch a dial or worry about selecting the incorrect function. The PDMM-20's

sophisticated microprocessor chip technology knows what you are measuring. Low impedance means that stray or "ghost" voltage is eliminated. The PDMM-20 also has a non-contact voltage detection feature! Just think, with one little tester you get all this performance!

Just like all Greenlee test and measurement products, the PDMM-20 is backed by a Lifetime Limited Warranty. With a safety rating of Category III 300V, the PDMM-20 is the tool for your everyday electrical needs.

## PRODUCT FEATURES

- **Auto-select mode** for hassle free use.
- **Low impedance** eliminates stray or "ghost" voltage readings.
- **AC/DC voltage** measurement.
- **Hassle free**, automatic measurement of voltage and resistance.
- **Autoranging** for quick, convenient measurements.
- **Non-contact voltage detection** for identifying live lines without contacting conductors.
- **Intelligent Auto-Off** for longer battery life.
- **Low battery indicator**.
- **Resistance** measurement.
- **Audible continuity** test.
- **Frequency measurement** in voltage mode.
- **Capacitance** measurement.
- **6000-count LCD** for high resolution.
- **Lifetime** Limited Warranty.

### Contents/Accessories -

- (1) 3 V battery (CR2032)
- Carry Case

## SPECIFICATIONS

**Voltage measurement:** 6.00, 60.00, 450.0 V

**Resistance measurement:** 600.0  $\Omega$ ; 6.000, 60.00, 600.0 k $\Omega$ ; 6.000 M $\Omega$

**Capacitance:** 100.0, 1000  $\eta$ F; 10.00, 100.0 mF

**Display:** 6000-count LCD

**Measurement Category:** CAT II, 450 V per IEC 61010-1; CAT III, 300 V per UL-3111-1

## ORDERING INFORMATION

| CAT. NO. | UPC NO. | DESCRIPTION         | QTY |
|----------|---------|---------------------|-----|
| PDMM-20  | 11689   | MULTIMETER, POCKET1 |     |



### DISTRIBUTED BY



**GREENLEE®**  
A Textron Company

|               |                 |                      |
|---------------|-----------------|----------------------|
| USA           | 800-435-0786    | Fax: 800-451-2632    |
|               | 815-397-7070    | Fax: 815-397-1865    |
| Canada        | 800-435-0786    | Fax: 800-524-2853    |
| International | +1-815-397-7070 | Fax: +1-815-397-9247 |

4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070  
©2004 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA  
Greenlee Textron Inc. is a subsidiary of Textron Inc.

[www.greenlee.com](http://www.greenlee.com)

MA-4604 09/04