



WCY88

WEJTAP CONN YEL

ACTIVE



Electrical division

☒ [Email Datasheet](#) [Print Datasheet](#)

FCI Brings You More

- ☒ [Contact our sales/technical support](#)
- ☒ [Sample request](#)
- [Price request](#)

Download document

Literature

- [> Wejtap Material Safety Data Sheet - Power Cell](#)
- [> Wejtap Material Safety Data Sheet - Black Powder Solvent](#)
- [> Wejtap Product Focus](#)
- [> Wejtap Brochures](#)
- [> Connector Theory and Application Brochure](#)

Application Tooling

- [> Electrical Tooling](#)

Specifications

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Conductor Size (Run - Diameter)			0.893 to 1.25
Conductor size (Run - Max)			1033.5-36/1
Conductor size (Run - Min)			954
Conductor Size (Run - mm)			23 mm² to 32 mm²
Conductor Size (Run)			1033.5-36/1
			1033.5
			954.0-36/1
			954
Conductor size (Tap - Max)			1000
Conductor size (Tap - Min)			795
Conductor Size (Tap)			795.0-36/1
			795
			1000
			954
Conductor Type (Run)			ACSR
			AAC
Wire Size			AWG
Wire Size (Tap - Diameter - in)			0.971 to 1.211
Wire Size (Tap - mm)			25 mm² to 31 mm²
Wire Type (Tap)			ACSR
			AAC
			Copper
Physical			
Color Code			Yellow
Approvals / Certifications			
UL Listed			No
CSA Certified			No
Other Features			
Installation Tool			WTY
Booster			WPBY Box 25
UPC			78181087580
Keyw ord			w ejtap