

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [64002-1215](#)
Status: **Active**
Description: 2.50mm Pitch, Wire-to-Board Housing, Female, 12 Circuits, UL94HB, Gray with White TPA™

Documents:

[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-104000-001 \(PDF\)](#)
[Packaging Specification PK-64002-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Housings
Series [64002](#)
Application Power, Wire-to-Board
Product Name N/A
UPC 756054579169

Physical

Circuits (maximum) 12
Color - Resin Gray, Natural
Gender Female
Glow-Wire Compliant No
Keying to Mating Part N/A
Lock to Mating Part None
Material - Resin Polyester
Net Weight 2.960/g
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.50mm
Pitch - Termination Interface 2.50mm
Polarized to Mating Part Yes
Ports 1
Stackable No
Temperature Range - Operating -30°C to +85°C

Material Info

Reference - Drawing Numbers

Packaging Specification PK-64002-001
Product Specification PS-104000-001
Sales Drawing SD-64002-001




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[64002Series](#)

Mates With

[53874](#) Wire-to-Board Header, [68145](#) Wire-
to-Board Header, [68151](#) Wire-to-Board
Header

Use With

[50654](#) Female Crimp Terminal