

PRODUCT NUMBER


71600-YXXLF

LEAD FREE, SEE NOTE 6

TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2


OPTIONAL STRAIN RELIEF
SEE SHEET 2

TRIANGLE INDICATES
POSITION 1
NOTE 5



NOTES:

- 1 - PLASTIC MAT'L : GLASS FILLED HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: GREY
- 2 - PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PRODUCT PACKAGED IN TUBES.
- 4 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
- 5 - 2x5, 2x6, 2x7 HAVE NO LEFT POLARIZING SLOT.
- 2x2, 2x3 WITH CENTRAL KEY HAVE NO TRIANGLE, NO LEFT AND RIGHT POLARIZING SLOT.
- 2x2 WITHOUT CENTRAL KEY HAS NO LEFT AND RIGHT POLARIZING SLOT.
- 2x3, 2x4 WITHOUT CENTRAL KEY HAVE NO LEFT POLARIZING SLOT
- 2x4 WITH CENTRAL KEY HAVE NO LEFT AND RIGHT POLARIZING SLOT
- 6 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008.
PACKAGING SPECIFICATION AS PER GS-14-920.



mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family 2.54MM IDC
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
AP	F12-0046	LMU	12.04.25	angles	X.X ±0.3		QUICKIE III FEM
AR	B-17851	LMU	14.06.05	linear	X.XX ±0.13		0.76µm Au
					X.XXX ±0.05	scale 5:1	
AK	F05-0180	LMU	05.04.22	dr	D.LE	01.01.24	dwg no
AL	F06-0270	LMU	06.09.12	engr	P.NZ	01.01.24	sheet 1 of 2
AM	F06-0274	LMU	06.09.25	chr	JF.N	01.01.24	size
AN	F09-0233	LMU	09.12.15	appd	P.NZ	01.01.24	A3
sheet	revision	AR	AF				type
index	sheet	1	2				CUSTOMER Drawing







Copyright FCI


form: A3

STRAIN RELIEF OPTION AVAILABILITY	Nbr OF POSITIONS
1/6	04
0/1/2/3/6	06
0/1/2/3/6	08
0/1/2/3/6	10
0/1/2/3/6	14
0/1/2/3/6	16
0/1/2/3/6	18
0/1/2/3/6	20
0/1/3	24
0/1/2/3/6	26
0/1/2/3/6	30
0/1/2/3/6	34
0/1/2/3/6	40
0/1/2/3/6	50
0/1/2/3/6	60
0/1/2/3/6	64
PLATING 0.76µm GOLD ON CONTACT AREA 1.27 µm Ni REMAINDER OF PRODUCT	


624
304
204 / 224
004
DASHES NOT AVAILABLE

LOW PROFILE
STRAIN RELIEFSTANDARD
STRAIN RELIEFLATCHING STRAIN RELIEF
FOR SLIM HEADER


WITHOUT STRAIN RELIEF



WITH LOW PROFILE STRAIN RELIEF



WITH STANDARD STRAIN RELIEF



WITH LATCHING STRAIN RELIEF

71600-6YYLF	●					●
71600-3YYLF		●	●			
71600-2YYLF	●				●	
71600-1YYLF	●				●	
71600-0YYLF	●		●			
PRODUCT NUMBER	WITH	WITHOUT	STANDARD	WITHOUT	LOW PROFILE	LATCHING
	CENTRAL KEY		STRAIN RELIEF			

mat'l. code				surface	tolerance	projection	product family
ltr	ecn no	dr	date	ISO 1302	ISO 406	ISO 1101	QUICKIE
AF	B-17851	LMU	14.06.05	tolerances unless otherwise specified			
				angles	linear	mm	title
AA	F10199	GCO	01.04.26			scale N/A	IDC RECEPT DR
AB	F03019	DLE	03.01.23	dr	D.LE	01.01.24	
AC	F05-0180	LMU	05.04.22	engr	P.NZ	01.01.24	
AD	F06-0270	LMU	06.09.12	chr	JF.N	01.01.24	
AE	F06-0274	LMU	06.09.25	appd	P.NZ	01.01.24	
sheet index	revision sheet						dwg no
							71600
							sheet 2 of - size
							A3
							type
							CUSTOMER Drawing

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[71600-024LF](#) [71600-120LF](#) [71600-350LF](#)