



Dimensions (In.)
(except where noted)

Specifications:

- Type: unshielded mono phone w/metal thread
- Dielectric strength: 500VAC for 1 minute
- Insulation resistance: 100MΩ @ 500VDC
- Contact resistance: 50mΩ max.
- Body & cap: ABS resin
- Terminal & contact: nickel plated brass
- Pin: nickel plated steel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-3500](#)