

MODEL:
Switched PDU



MODEL NUMBER:
OSP-V-20-11-16-N1



Features

Current Meter	Digital True RMS Current Meter
Power Monitor	Remote Total Power Monitoring by Meter, Web, SNMP, Free Bundle Software
Protocols	http, https, SNMP, DHCP, UDP
Outlet Control	Individual Outlet Control
Power Delay	Power On/Off Sequence can be Defined
Alarm Thresholds	User-Defined Alarm Thresholds for Warning and Overload
Event Alert	Email, Trap, Audible Alarm

Specification:

General	Communication	Operation
Output: (16) NEMA 5-20/15R Input: (1) IEC320 C20 Inlet; Enclosed IEC320 C19 to NEMA 5-20P Power Cord 3 Meters long Protection (1) 20 Amp Circuit Breaker	SSL Indication (1) Yellow LED DHCP Indication (1) Green LED Output Status (16) Red LED Network (1) RJ45 for Ethernet Current Meter 3 Digits Seven Segments for True RMS Meter Range: 0A ~ 20A Resolution: 0.1A Precision: +/-2%+/-0.1 Amp	Nominal Voltage 115V Voltage 100V~ 127V full range Frequency 50/60HZ full range Max. Output Current 20 Amp (UL derated 1 Amp) Temperature 0 ~ 40 Celsius degree Humidity 0% ~ 90% Size 56 x 1245 x 44 mm Weight 4 kg

Regulatory Approvals:

UL 60950-1, UL Listed, CSA, cUL Listed, CB by UL
CE, EN 55022 Class A, EN 5024, EN 61000-3-2, EN 61000-3-3, C-Tick AS/NZS CISPR 22: 2006
FCC Part 15 Class A, ICES-003