

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


0678551107

Status:

Obsolete

Description:

Audio Jack Stacked PCB Receptacle, Shielded, 0.38μm (15μ") Gold (Au) Plating, 13 Circuits, with 3 Color Coded Ports, Lead Free



Documents:

Drawing (PDF)

General	
Product Family	I/O Connectors
Series	67855
Application	Wire-to-Board
Comments	Port A color: Pink Port B color: Blue Port C color: Green
Component Type	Receptacle
Product Name	Audio/Phono Jack
Type	N/A
Physical	
Boot Color	N/A
Circuits (Loaded)	13
Circuits (maximum)	13
Gender	Jack
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Number of Rows	3
Orientation	Right Angle
PC Tail Length	2.20mm (.087")
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	1.25mm (.049")
Pitch - Termination Interface	1.25mm (.049")
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +85°C
Waterproof / Dustproof	No
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	1A
Grounding to Panel	Press-Fit
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	150V DC
Material Info	

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

67855Series

Mates With

Audio Plug

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION