

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect





ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-4 @20°C	0.11 ohms ±20%
D.C. RESISTANCE	7-9 @20°C	0.30 ohms ±10%
INDUCTANCE	2-4 100kHz, 100mVAC, Ls	180uH ±10%
INDUCTANCE	7-9 100kHz, 100mVAC, Ls	95uH ±10%
DIELECTRIC	4-7 1250VAC, 1 second	1000VAC, 1 minute
URNS RATIO	(4-2):(7-9)	1.384:1, ±1%

GENERAL SPECIFICATIONS:

6B OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE	PART NO.
6B	12/10	Method: Tray PKG-0318 www.we-online.com/midcom		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	TRANSFORMER	750311524
6A	5/10	SEE REVISION SHEET FOR REVISION LEVEL				

eiSos p/n: 750311524



SPECIFICATION SHEET 1 OF 1