





SPECIFICATIONS

Material: Silicone rubber conforms to A-A-59588, Class III, GR50 (unless otherwise specified).
Mounting Nut: Brass, nickel-plated
Temperature Range: -94° F to +400° F (-70° C to +204° C).
Pressure Range: Exceeds 15 psi internal and 1500 psi external.
Operational Life: 50,000 actuations (minimum).
Shelf Life: Excess of 25 years.
Resistant to: Salt spray, sunlight, ozone, weather, fungus, and most acids and lubricating oils.
Agency Recognition: UL & ULC Recognized to UL Std. 50



ALL DIMENSIONS ARE IN INCHES[MM].
TOLERANCES: UNLESS OTHERWISE NOTED $\pm 1/32$ [± 0.793].

REV.	DESCRIPTION			DATE
MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION.	TITLE: BOOT, TOGGLE SWITCH FULL COVER			ENG. DAN LAW 04.10.13
				DWN: DAN LAW 04.10.13
MAT'L: SILICONE RUBBER A-A-59588, Gr.50	APM-HEXSEAL CORPORATION			CHKD. F. KONCHALSKI 04.26.13
FINISH: BLACK				SCALE 2.5:1 DWG.NO. 1131/31 17

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.
THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.