

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INC. IT IS SUBJECT TO CHANGE AND THE
CONTROLLING ENGINEERING ORGANIZATION SHOULD
BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

COPYRIGHT 2000

BY AMP INCORPORATED ALL RIGHTS RESERVED

APPLICATOR PARTS LIST				TYPE HINGEBAR MARK IV			AMP INCORPORATED HARRISBURG, PENNA.			
NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.	CRIMPING DATA		TERMINALS
1	WIRE CRIMPER	1	458596-2	42	BAR, FRONT STAB	1	456260-1	TO APPLY TERMINAL (BUSSING) TAB LOK		760 FEED 62021
2	INS. CRIMPER			43	HOLD DOWN, HINGE BAR	1	811009-1	WIRE SIZE	CRIMP HEIGHT	
3	ANVIL	1	843101-1	44	HINGE BLK. & STAB	1	810974-1	18	.052	
4	ANVIL INSERT	1	456262-1	45	HINGE PIN	1	811007-1	16	.056	
5				46	GUARD FRONT	1	456599-1	14	.062	
6	REAR SHEAR PLATE	1	456271-2	47	ASSY HINGE BAR	1	459928-1	12	.072	
7	DEFLECTOR, CHIP	1	459942-1	48	SPRING, HINGE BAR	2	3-23846-5	SEE REMARKS		
8	SHEAR, FLOATING	1	459926-1	49				CRIMP	SIZE	TYPE
9	PLT, RETAINING REAR	1	459924-1	50				WIRE	.160	TL
10	FRONT ANVIL SPACER PLT.			51	SPACER, COMP SPRING	2	811070-1	INSUL.	-H-	SEE
11	SPACER, ANVIL HOLDER	1	811223-1	52				SLEEVED	-H-	TERMINAL
12	CRIMP SPACER			53				INSULATION RANGE	WIRE RANGE	
13	FRONT STRIP GUIDE	1	456257-1	54	PLATE IDENTIFICATION	1	452373-1	-H-	18-12	
14	REAR STRIP GUIDE	1	456258-1	55	SLR, DRIVE	3	21017-6	EXPLODED VIEW PLM A-6004-9		
15	RAM STD H.B. RAM	1	473828	56				REMARKS:		
16	PLT, RAM RETAINING	1	465004-2	57				RIGHT HAND		620 FEED
17	WEAR PLT, RAM	1	811010-1	58				2# 18 - .058		62091
18	PROTECTIVE PLUG	1	23141-1	59				#18 + #16 - .060		
19	APPLICATOR MOUNT ASSY.			60				2# 16 - .064		
20	BASE PLATE	1	456252-1	61				FOR TERMINAL 62021		
21	BLOCK, SHEAR RET.	1	459927-1	62				PRIOR TO REV W OR		
22	STRIP GUIDE PLATE			63				FOR TERMINAL 62091		
23	ANVIL HOLDER	1	810423	64	SPRING SHEAR RETURN	1	7-22282-3	PRIOR TO REV U, USE		
24	AUX. ANVIL HOLDER			65				ANVIL P/N 692901-1		
25	STRIPPER			66				DENOTES WEARING PARTS		
26	STRIPPER MOUNT			67				RECOMMEND PURCHASE REPLACEMENT		
27	RETAINER PLATE			68				THIS APPLICATOR IS TO BE USED ON		
28	STRIPPER MOUNT BRACKET			69				AMP-O-LECTRIC 1-471273-2		
29	STRIPPER BUSHING			70	SPACER, FEED SWIVEL	2	452064-1	AMP-O-MATIC		DIST.
30	STOCK DRAG	1	387650-4	71	BAR, EXTENSION AIR FEED	1	672036-1	SERIAL NO.		DATE SHIPPED
31	STOCK DRAG HANDLE			72	ASSY AIR FEED	1	1-690821-3	CUSTOMER NAME AND ADDRESS		DESIGNED
32	STOCK DRAG STUD	1	370573	REV.	REVISION RECORD	DATE	BY	ECN	CHK'D	
33	STOCK DRAG SPRING	1	370572	A	REV. PER ECN	1/15/76	JL	81491	9-28-73	
34	STOCK DRAG ADJ. SCREW			B	REV. PER ECN	9/19/76	JL	81547	9-28-73	
35	FEED FINGER ASYM	1	810131	C	ADD ITEM 70 PER ECN	1-9-79	KS	812834	9-28-73	
36	FEED FINGER	1	811644-1	D	ECN A-055788	3/11/88	DS		9-28-73	
37	FEED FINGER TIP	1	811645-2	E	ECN A-105788	6-23-88	MD		9-28-73	
38	DOWEL PIN, FEED FINGER	2	1-21030-3	F	ECN A-170588	12-88	NE		9-28-73	
39	BASE CASTING	1	570238	G	0150-7303-96	10-96	DS		9-28-73	
40	GUARD	1	456598-1	H	ECN 0150-0208-04	2-04	MY		9-28-73	
41	BRACKET, GUARD	1	454948-1			3-04	MY		9-28-73	

CAGE CODE
00778

CUSTOMER AND ASSEMBLY DRAWING

RESTRICTED TO

(COPY - ORIGINAL DESTROYED)

Rad

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
 AMPLING IT IS SUBJECT TO CHANGE AND THE
 CONTROLLING ENGINEERING ORGANIZATION SHOULD
 BE CONTACTED FOR THE LATEST REVISION.

APPLICATOR PARTS LIST (BOLT, NUT, SCREW, WASHER etc.)

NO.	DESCRIPTION	SIZE	LGTH.	REQ.	PART NO.	NO.	DESCRIPTION	SIZE	LGTH.	REQ.	PART NO.
101	SCR, SOC. HD. CAP HINGE BLK.	5/16-18	.75	3	1-21001-8	142					
102	SCR, SOC. HD. CAP HINGE BLK.	1/4-20	.62	2	21001-3	143					
103	SCR, SOC. SET (SELF LK) HINGE BLK.	#8-32	.25	1	4-21008-0	144					
104	SCR, SOC. HD. CAP FRONT STAB.	5/16-18	.75	2	1-21001-8	145					
105	PIN, SLT. SPRING FRONT STAB.	.250 DIA	1.00	2	4-21029-7	146					
106						147					
107	SCR, SOC. HD. CAP ANVIL HOLDER	#10-32	.75	2	3-21000-7	148					
108	SCR, SOC. SET (LOC W/L) SPR. HINGE BAR	1/2-13	1.00	2	4-21009-7	149					
109	SCR, HEX HD. MACH H.B. HOLD DOWN	5/16-18	.75	2	1-21015-6	150					
110						151					
111	SCR, SOC. HD. CAP ANVIL INSERT	#8-32	.38	2	2-21000-6	152					
112	SCR, SOC. SET (1/2 DOC) SHEAR HLD	1/4-20	.50	1	21007-6	153					
113	NUT, HEX MACH SHEAR HLD	1/4-20	—	1	21019-1	154					
114	SCR, SOC. HD. CAP SHEAR HLD	#10-32	.88	2	3-21000-8	155					
115						156					
116						157					
117	SCR, BUTT. HD. CAP FR. STR. GDE	#10-32	.38	3	2-21002-6	158					
118	SCR, SOC. HD. CAP. REAR STR GDE	#10-32	.62	3	3-21000-6	159					
119	WASHER, FLAT " " "	# 8	—	3	1-21899-3	160					
120						161					
121											
122	NUT, HEX MACH DRAG	#10-32	—	1	21018-7	162					
123	NUT, HEX MACH S/L DRAG	#10-32	—	1	21021-4	163					
124						164					
125	SCR, SOC. SET (LOK W/L) DRAG	#6-32	.25	1	2-21008-9	165					
126	SCR, SOC. HD. CAP CRIMPER	1/4-20	1.00	2	21001-6	166					
127	SCR, SOC. SET (LOK W/L) RAM PIN	1/4-20	.38	1	21009-4	167					
128											
129											
130	SCR, SOC. SET RAM CAP	1/4-28	1.00	2	1-21007-7						
131	NUT, HEX HD MACH RAM CAP	1/4-28	—	2	21019-7						
132	SCR, HEX HD CUP	3/8-16	1.25	2	3-21015-2						
133	WASHER, BASE MOUNT			2	371178						
134	SCR, SOC. HD. CAP BAREXT. AIR FEED	1/4-20	1.00	4	21001-6						
135	SCR, SOC. SET (LOK W/L) FEED FINGER	#8-32	.25	4	4-21008-0						
136	SCR, SOC. HD. CAP FEED FINGER TIP	#8-32	.25	1	2-21000-5						
137	WASHER, FLAT	1/4		2	21899-3						
138											
139	SCR, BUT HD CAP	4-40	.25	1	1-21002-3						
140											
141	SCR, BUT HD CAP	6-32	.25	1	1-21002-6						

APPLICATOR ONLY TO INCLUDE

NOTES:

REV.	APPLICATOR PART LIST	SHEET
H	566104-2	2 OF 2

THIS DRAWING IS UNCLASSIFIED
 COPYRIGHT 2000
 BY AMP INCORPORATED ALL RIGHTS RESERVED
 RELEASED FOR PUBLICATION

CUSTOMER AND ASSEMBLY DRAWING

00779

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[566104-2](#)