

SMT TOROID CHOKE


ASTC-12 SERIES



STANDARD SPECIFICATIONS:

P/N ASTC-12-	Lp $\mu\text{H} \pm 20\%$	DCR $\text{m}\Omega$ Max	DC Bias A	L w/ Bias $\mu\text{H} \pm 20\%$	ET Min V- μsec
10R4-3.8	10.4	31	3.8	9.4	15.2
14R6-3.13	14.6	45	3.13	13.3	18.8
250-2.43	25	74	2.43	23	24.3
560-1.65	56	141	1.65	50	37.0
830-1.35	83	213	1.35	75	44.3
101-1.23	100	288	1.23	90	49.2
151-0.99	152	445	0.99	137	59.4
221-0.81	220	668	0.81	200	71.3
331-0.65	331	1026	0.65	305	85.8
471-0.53	472	1530	0.53	439	99.6

PHYSICAL CHARACTERISTICS:



TECHNICAL INFORMATION:

- Testing frequency: 100KHz, 0.1VRMS
- Add -T for Tape and Reel
- RoHS compliance effective 0527, label on reel and box