


DATE	SYM	REVISION RECORD	AUTH	DR.	CK.
11/26/05	A	ADDED "ROHS COMPLIANT"	T.B.	B.S.	
3/11/06	B	UPDATED MATERIAL SPEC.	T.B.	B.S.	
5/06/06	C	ADDED CONTACT RESI. INFO.	T.B.	B.S.	
1/12/08	D	RANGE WAS "RANGEE"	T.B.	B.S.	



ORDERING CODE BC22AA

SOLDER LUGS = L
(6") WIRE LEADS = W
9 VOLT TYPE SNAPS = SF

WIRE LEADS SHOWN ABOVE

SPECIFICATIONS :

Plastic material - polypropylene
 Flammability Rating-UL94 HB, UL File No. E216959
 Temperature Range: -10°C to +100°C
 Springs - nickel plated spring steel
 Wire - 152.4 mm Long 26 AWG, UL1007, CSA - TR-64, 300V, 80° C.
 Rivets - Brass, nickel plated
 9 Volts Snaps - Brass, nickel plated
 Contact Resistance: Under 50mΩ for +/- contacts per EIA-540J000
 ROHS COMPLIANT

Note: Dimensions in mm. (inches)

TOLERANCES (EXCEPT AS NOTED)	 Memory Protection Devices, Inc. 200 Broad Hollow Road, Farmingdale, New York 11735		
DECIMAL + .5 (.020") - .5 (.020")	TITLE TWO "AA" CELL HOLDER	SCALE NONE	DRAWN BY S.C.
FRACTIONAL + .8 (.030") - .8 (.030")		APPROVED BY	
ANGULAR + 3° - 3°	DATE 1/12/2008	DRAWING NUMBER BC22AAW	