

LTR	REV.	DESCRIPTION	DATE
△	C	ECN # 021007-5 CHANGE PACKING	10/07/02

NOTES:

- CABLE:**
UL-2725 24AWG*2C+28AWG*1PR+AL-FOIL
+DRAIN WIRE+BRAID(65%),PVC JACKET.
△ COLOR:WHITE(NK-W05) ,OD:4.7±0.15mm .
- CONNECTORS:**
P1&P2:USB A TYPE MALE GOLD FLASH CONTACT
NICKEL PLATED SHELL.
- HOOD:**MOLDED TYPE,PVC 45P,COLOR:WHITE(NK-W05)
- TEST REQUEST:**
<1>.100% OPEN SHORT & MIS WIRE TEST.
<2>.CONTACT RESISTANCE 3 Ohms MAX.
<3>.INSULATION RESISTANCE 20M Ohms MIN.
- PACKING:**EACH PC / BLISTER (BLISTER CARD WITH DIGITUS
ARTWORK PROVIDED BY CUSTOMER) + EAN CODE
- DRIVE DISK** 1PC.
- EAN-CODE:** DN-3002 (4016032117902)
DN-3003 (4016032117919)

P1		P2	
RED	1	1	
WHITE	2	2	
GREEN	3	3	
BLACK	4	4	

ENGINEER ISSUE

OCT 08 2002

APPROVED:

SHELL		BRAID		SHELL	

DWG NO.	NEOSTAR P/N	E-SSM P/N	PRODUCT	PVC MOLD	IC
170-0770-1	USL-1012	DN-3002	1*USB TO 1*USB	USB LINK CABLE	GL620USB
170-0770-2	USL-1162	DN-3003	1*USB TO 16*USB	USB NETLINK CABLE	GL620USB-A

Tolerance Inch M/M			ASSMANN Electronics	
.X	.015	.30	Title USB DATA LINK CABLE 2.0	
.XX	.010	.10		
.XXX	.005	.05		
Draw KIKI 10/07			Customer P/N	
Check			App'd Customer E-SSM	
Engr			Scale NONE Units m/m Third Angle Projection	
			Dwg No. 170-0770 REV C Sheet 1/1	