


# SDA Series Low Profile DIP Switches

## Features/Benefits

- Low profile design saves space
- Thru-hole and surface mount models
- Tape and reel packaging available
- RoHS compliant

## Typical Applications

- Address switch for industrial controls
- Logic switching for computers and peripherals
- Function controlling for numerous applications



H

DIP

## Specifications

CONTACT RATING: 25 mA @ 24 V DC or 100 mA @ 5 V DC.  
MECHANICAL AND ELECTRICAL LIFE: 1,000 cycles at rated loads.  
CONTACT RESISTANCE: 50 mΩ max. initial.  
INSULATION RESISTANCE: 100 MΩ between terminals.  
DIELECTRIC WITHSTANDING VOLTAGE: 300 V DC min. for 1 minute.  
STORAGE TEMPERATURE: -40°C to 85°C.  
OPERATING TEMPERATURE: -40°C to 85°C.  
OPERATING FORCE: 800 grams max.  
SOLDERABILITY: Dip and look solderability testing per C&K spec. #448. Unplated edges of terminals permitted.  
PACKAGING: Switches supplied in rigid dispensing tubes in full-tube quantities only, this may affect order quantity. Numbers of switches per tube varies with model. Tape and reel packaging also available for surface mount options.

## Materials


HOUSING: PPS, color black (UL94V-0).  
COVER: PPS, color black (UL94V-0).  
ACTUATOR: PA6T (UL94-0)  
CONTACTS: Gold plated Beryllium copper.  
TERMINALS: Gold plate over nickel plated brass.  
TAPE SEAL: Polyimide.

**Note:** Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center. For Tin Lead options consult customer service center.

## How To Order

The Build-A Switch concept allows you to mix and match options to create the switch you need. Below is a complete listing of options shown in catalog. To order, simply select desired option from each category and place in the appropriate box.

All switches supplied in "OFF" position..



Dimensions are shown: Inch (mm)  
Specifications and dimensions subject to change


# SDA Series

## Low Profile DIP Switches




DIP

### Flush Actuator – No Tape, Thru-hole Terminals



| ROHS<br>PART NUMBER | NO.<br>POS. | DIM. 'A'      | QUANTITY<br>PER TUBE |
|---------------------|-------------|---------------|----------------------|
| <b>SDA01H0BD</b>    | 1           | .178 (4,52)   | 100                  |
| <b>SDA02H0BD</b>    | 2           | .278 (7,06)   | 60                   |
| <b>SDA03H0BD</b>    | 3           | .378 (9,60)   | 45                   |
| <b>SDA04H0BD</b>    | 4           | .476 (12,10)  | 35                   |
| <b>SDA05H0BD</b>    | 5           | .578 (14,68)  | 30                   |
| <b>SDA06H0BD</b>    | 6           | .676 (17,18)  | 25                   |
| <b>SDA07H0BD</b>    | 7           | .778 (19,76)  | 20                   |
| <b>SDA08H0BD</b>    | 8           | .876 (22,26)  | 20                   |
| <b>SDA09H0BD</b>    | 9           | .978 (24,84)  | 15                   |
| <b>SDA10H0BD</b>    | 10          | 1.076 (27,34) | 15                   |
| <b>SDA12H0BD</b>    | 12          | 1.279 (32,50) | 14                   |
| Schematic           |             |               |                      |
| SPST                |             |               |                      |

### Flush Actuator – With Top Tape, Thru-hole Terminals



| ROHS<br>PART NUMBER | NO.<br>POS. | DIM. 'A'      | QUANTITY<br>PER TUBE |
|---------------------|-------------|---------------|----------------------|
| <b>SDA01H0B</b>     | 1           | .178 (4,52)   | 100                  |
| <b>SDA02H0B</b>     | 2           | .278 (7,06)   | 60                   |
| <b>SDA03H0B</b>     | 3           | .378 (9,60)   | 45                   |
| <b>SDA04H0B</b>     | 4           | .476 (12,10)  | 35                   |
| <b>SDA05H0B</b>     | 5           | .578 (14,68)  | 30                   |
| <b>SDA06H0B</b>     | 6           | .676 (17,18)  | 25                   |
| <b>SDA07H0B</b>     | 7           | .778 (19,76)  | 20                   |
| <b>SDA08H0B</b>     | 8           | .876 (22,26)  | 20                   |
| <b>SDA09H0B</b>     | 9           | .978 (24,84)  | 15                   |
| <b>SDA10H0B</b>     | 10          | 1.076 (27,34) | 15                   |
| <b>SDA12H0B</b>     | 12          | 1.279 (32,50) | 14                   |
| Schematic           |             |               |                      |
| SPST                |             |               |                      |



# SDA Series Low Profile DIP Switches

## Flush Actuator – With Top Tape, Surface Mount Terminals

| ROHS<br>PART NUMBER | NO.<br>POS. | DIM. 'A'      | QUANTITY<br>PER TUBE |
|---------------------|-------------|---------------|----------------------|
| <b>SDA01H0SB</b>    | 1           | .178 (4,52)   | 100                  |
| <b>SDA02H0SB</b>    | 2           | .278 (7,06)   | 60                   |
| <b>SDA03H0SB</b>    | 3           | .378 (9,60)   | 45                   |
| <b>SDA04H0SB</b>    | 4           | .476 (12,10)  | 35                   |
| <b>SDA05H0SB</b>    | 5           | .578 (14,68)  | 30                   |
| <b>SDA06H0SB</b>    | 6           | .676 (17,18)  | 25                   |
| <b>SDA07H0SB</b>    | 7           | .778 (19,76)  | 20                   |
| <b>SDA08H0SB</b>    | 8           | .876 (22,26)  | 20                   |
| <b>SDA09H0SB</b>    | 9           | .978 (24,84)  | 15                   |
| <b>SDA10H0SB</b>    | 10          | 1.076 (27,34) | 15                   |
| <b>SDA12H0SB</b>    | 12          | 1.279 (32,50) | 14                   |

Schematic

SPST



SDA08H0SB



H

DIP


NOTE: SDA 01 options are 4,25mm thick

## Flush Actuator – No Tape, Surface Mount Terminals

| ROHS<br>PART NUMBER | NO.<br>POS. | DIM. 'A'      | QUANTITY<br>PER TUBE |
|---------------------|-------------|---------------|----------------------|
| <b>SDA01H0SBD</b>   | 1           | .178 (4,52)   | 100                  |
| <b>SDA02H0SBD</b>   | 2           | .278 (7,06)   | 60                   |
| <b>SDA03H0SBD</b>   | 3           | .378 (9,60)   | 45                   |
| <b>SDA04H0SBD</b>   | 4           | .476 (12,10)  | 35                   |
| <b>SDA05H0SBD</b>   | 5           | .578 (14,68)  | 30                   |
| <b>SDA06H0SBD</b>   | 6           | .676 (17,18)  | 25                   |
| <b>SDA07H0SBD</b>   | 7           | .778 (19,76)  | 20                   |
| <b>SDA08H0SBD</b>   | 8           | .876 (22,26)  | 20                   |
| <b>SDA09H0SBD</b>   | 9           | .978 (24,84)  | 15                   |
| <b>SDA10H0SBD</b>   | 10          | 1.076 (27,34) | 15                   |
| <b>SDA12H0SBD</b>   | 12          | 1.279 (32,50) | 14                   |

Schematic

SPST




SDA08H0SBD

NOTE: SDA 01 options are 4,25mm thick

## Extended Actuator – No Top Tape, Thru-hole Terminals



SDA08H1BD




NOTE: SDA 01 options are 4,25mm thick

| ROHS<br>PART NUMBER | NO.<br>POS. | DIM. 'A'      | QUANTITY<br>PER TUBE |
|---------------------|-------------|---------------|----------------------|
| <b>SDA01H1BD</b>    | 1           | .178 (4,52)   | 100                  |
| <b>SDA02H1BD</b>    | 2           | .278 (7,06)   | 60                   |
| <b>SDA03H1BD</b>    | 3           | .378 (9,60)   | 45                   |
| <b>SDA04H1BD</b>    | 4           | .476 (12,10)  | 35                   |
| <b>SDA05H1BD</b>    | 5           | .578 (14,68)  | 30                   |
| <b>SDA06H1BD</b>    | 6           | .676 (17,18)  | 25                   |
| <b>SDA07H1BD</b>    | 7           | .778 (19,76)  | 20                   |
| <b>SDA08H1BD</b>    | 8           | .876 (22,26)  | 20                   |
| <b>SDA09H1BD</b>    | 9           | .978 (24,84)  | 15                   |
| <b>SDA10H1BD</b>    | 10          | 1.076 (27,34) | 15                   |
| <b>SDA12H1BD</b>    | 12          | 1.279 (32,50) | 14                   |

Schematic

SPST



Third Angle  
Projection

Dimensions are shown: Inch (mm)

Specifications and dimensions subject to change


# SDA Series

## Low Profile DIP Switches

### Extended Actuator – No Top Tape, Surface Mount Terminals



SDA08H1SBD



NOTE: SDA 01 options are 4,25mm thick





| ROHS PART NUMBER | NO. POS. | DIM. 'A'      | QUANTITY PER TUBE |
|------------------|----------|---------------|-------------------|
| SDA01H1SBD       | 1        | .178 (4,52)   | 100               |
| SDA02H1SBD       | 2        | .278 (7,06)   | 60                |
| SDA03H1SBD       | 3        | .378 (9,60)   | 45                |
| SDA04H1SBD       | 4        | .476 (12,10)  | 35                |
| SDA05H1SBD       | 5        | .578 (14,68)  | 30                |
| SDA06H1SBD       | 6        | .676 (17,18)  | 25                |
| SDA07H1SBD       | 7        | .778 (19,76)  | 20                |
| SDA08H1SBD       | 8        | .876 (22,26)  | 20                |
| SDA09H1SBD       | 9        | .978 (24,84)  | 15                |
| SDA10H1SBD       | 10       | 1.076 (27,34) | 15                |
| SDA12H1SBD       | 12       | 1.279 (32,50) | 14                |

Schematic

SPST

### Tape & Reel Packaging – Surface Mount Options only

| MODEL NO.                                | 'S' OPTION | DIM. 'H' (REF.) | DIM. 'W1' (REF.) | DIM. 'W2' (REF.) | DIM. 'B' (REF.) | DIM. 'C' (REF.) | DIM. 'D' (REF.) | QUANTITY PER REEL |
|------------------------------------------|------------|-----------------|------------------|------------------|-----------------|-----------------|-----------------|-------------------|
| SDA01                                    | H0         | 5.2             | 24.0             | 24.4             | 8.5             | 11.5            | N/A             | 1500              |
|                                          | H1         | 5.8             |                  |                  |                 |                 |                 | 1450              |
| SDA02                                    | H0         | 4.8             | 24.0             | 24.4             | 7.9             | 11.5            | N/A             | 750               |
|                                          | H1         | 5.8             |                  |                  |                 |                 |                 | 700               |
| SDA03                                    | H0         | 4.8             | 24.0             | 24.4             | 10.4            | 11.5            | N/A             | 750               |
|                                          | H1         | 5.8             |                  |                  |                 |                 |                 | 700               |
| SDA04                                    | H0         | 4.8             | 24.0             | 24.4             | 12.9            | 11.5            | N/A             | 750               |
|                                          | H1         | 5.8             |                  |                  |                 |                 |                 | 700               |
| SDA05                                    | H0         | 4.8             | 24.0             | 24.4             | 15.4            | 11.5            | N/A             | 750               |
|                                          | H1         | 5.8             |                  |                  |                 |                 |                 | 700               |
| SDA06                                    | H0         | 4.8             | 32.0             | 32.4             | 18.0            | 14.2            | 28.4            | 750               |
|                                          | H1         | 5.8             |                  |                  |                 |                 |                 | 700               |
| SDA07                                    | H0         | 4.8             | 32.0             | 32.4             | 20.5            | 14.2            | 28.4            | 750               |
|                                          | H1         |                 |                  |                  |                 |                 |                 | 700               |
| NOT CURRENTLY AVAILABLE IN TAPE AND REEL |            |                 |                  |                  |                 |                 |                 |                   |
| SDA08                                    | H0         | 4.8             | 44.0             | 44.4             | 22.7            | 20.2            | 40.4            | 750               |
|                                          | H1         | 5.8             |                  |                  |                 |                 |                 | 700               |
| SDA09                                    | H0         | 4.8             | 44.0             | 44.4             | 25.5            | 20.2            | 40.4            | 750               |
|                                          | H1         | 5.8             |                  |                  |                 |                 |                 | 700               |
| SDA10                                    | H0         | 4.8             | 44.0             | 44.0             | 28.1            | 20.2            | 40.4            | 750               |
|                                          | H1         | 5.8             |                  |                  |                 |                 |                 | 700               |
| SDA12                                    | H0         | 4.8             | 44.0             | 44.4             | 33.2            | 20.2            | 40.4            | 750               |
|                                          | H1         |                 |                  |                  |                 |                 |                 | 700               |
| NOT CURRENTLY AVAILABLE IN TAPE AND REEL |            |                 |                  |                  |                 |                 |                 |                   |



Dimensions are shown: Inch (mm)  
Specifications and dimensions subject to change

