



- Load rating up to 34kg
- 100% extension
- 12.7mm slide thickness
- Low profile - only 26.3mm high
- Hold-in

- Charge jusqu'à 34kg
- Course 100%
- Épaisseur de glissière de 12,7mm
- Section réduite: 26,3mm de haut seulement
- Point dur en position fermée

- Lastwert bis 34kg
- Vollauszug
- 12,7mm Schienendicke
- Geringe Schienenhöhe nur 26,3mm hoch
- Einhalterung - in geschlossener Position



| 2601        | mm  |     |     |     |     |     |     | kg   |    |
|-------------|-----|-----|-----|-----|-----|-----|-----|------|----|
|             | SL  | TR  | A   | B   | C   | D   | E   | W    | L  |
| DZ2601-0020 | 200 | 209 | 128 | -   | -   | -   | -   | 0.46 | 16 |
| DZ2601-0025 | 250 | 259 | 128 | -   | -   | -   | -   | 0.59 | 23 |
| DZ2601-0030 | 300 | 308 | 128 | 224 | -   | -   | -   | 0.69 | 32 |
| DZ2601-0035 | 350 | 357 | 128 | 224 | -   | -   | -   | 0.80 | 34 |
| DZ2601-0040 | 400 | 406 | 128 | 224 | 320 | -   | -   | 0.93 | 32 |
| DZ2601-0045 | 450 | 456 | 128 | 224 | 352 | -   | -   | 1.16 | 29 |
| DZ2601-0050 | 500 | 505 | 128 | 224 | 352 | 416 | -   | 1.18 | 30 |
| DZ2601-0055 | 550 | 554 | 128 | 224 | 352 | 448 | 489 | 1.29 | 27 |

#### Notes:

- Fixing recommendation: M4 screw.  
Max. head. ht. 2mm/Ø7.8mm

#### Notes:

- Visserie recommandée: Vis M4 hauteur de tête 2mm/Ø7.8mm

#### Hinweise:

- Empfohlene Befestigung: Schraube M4, max. Kopfhöhe 2mm/Ø7.8mm