


REV.	DATE	ECR NO.	DESCRIPTION
NC	02/03/09	—	INITIAL RELEASE



LENGTH TABLE	
PART NUMBER	LENGTH (IN.)
135101-04-06.00	6.00
135101-04-12.00	12.00
135101-04-24.00	24.00
135101-04-36.00	36.00
135101-04-48.00	48.00

NOTE:

1. PERFORM CONTINUITY AND HI-POT TESTING.
2. PACKAGED INDIVIDUALLY IN HEAT SEALED POLY BAG.

3	009-954-352	HEAT SHRINK TUBING, BLACK, 3/8" DIAMETER	A/R FT
2	009-881-377	COAXIAL CABLE, RG58/U	A/R FT
1	132113	CONNECTOR, SMA STRAIGHT PLUG, GOLD	2
	PN	DESCRIPTION	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm $\pm$ 0.20mm
8 - 30mm $\pm$ 0.40mm
30 - 120mm $\pm$ 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 - .315 = $\pm$ 0.007"
.315 - 1.180 = $\pm$ 0.015"
1.180 - 4.724 = $\pm$ 0.020"

DO NOT SCALE DRAWING

APPROVALS		DATE
DRAWN	G.R.S.	02/03/09
CHECKED		
ISSUED		
SHEET	1 OF 1	
CAD FILE	C:/135/135101-04-XX.XX.DWG	

Amphenol Connex

PART DESCRIPTION

SMA PLUG TO SMA PLUG, RG58

PART NO.

135101-04-XX.XX

DWG. NO.

135101-04-XX.XX.DWG

REV. NC

SIZE A

SCALE NA