


30 Option:
0.000030" gold on mating end,
tin-lead on termination end,
with entire contact nickel

Rated Current: 5A

Rated Voltage: 300v DC

Withstanding Voltage:
500v(r.m.s.) AC for 1 min

Insulation Resistance:
More than 1000Mohm at
500v DC

Contact Resistance: 13mohm Max.

Dielectric Strength: 1000v for 1 min

Temperature:
-55°C to +125°C

Item	Measured Value	Test Frequency
Z[ohm]	13 Min	30 MHz
Z[ohm]	20 Min	50 MHz
Z[ohm]	40 Min	100 MHz

CSA NRTL/C Certified File No. LR78160

REVISION	DATE	DESCRIPTION	DRAWN BY	DESIGNED BY	UNITS	KF 42-B25P/E9S-A4N	Right Angle, PCB Mount, Dual Port	
A1	6/2/99	New Drawing	K. Wallace		mm [in.]			
A2	7/7/99	Rev. PCB Dim.	CHECKED BY	APPROVED BY	DATE			
A3	12/27/99	Release Dwg			6/2/99		25 Pos. Male/9 Pos. Female 0.750" Spacing, Ferrite	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[K42-B25P/E9S-A4N](#) [K42-B25P/E9S-A4N15](#)