

[Request more info](#)**Part Number : 5219432F**

5219432F



This is a  
RoHS Compliant Product  
[To learn more click here](#)


**General Description**

Series	521
Configuration	3 mm Lens
Description	Discrete LED Lamp
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Single Color
Lens Color	Tinted Non-Diff

**Absolute Maximum Ratings (Ta = 25°)**

Forward Current mA	30mA
Reverse Current	100 @ Vr = 5V
Forward Current Pulsed	120mA
Derating	from 50° @ .4mA/°C
Solder Temperature	260° for 5 sec
Operating Temperature	-55~+100
Storage Temperature	-55~+100

**Operating Characteristics**

LED Type	Standard Efficiency
Color	Red 
Luminous Intensity Min	8.7
Luminous Intensity Typical	29
Test Current mA	20mA
Power Dissipation Max	100mW

[Share](#) |

|