



HIGH PERFORMANCE **E9225 series**

Size: (92 x 92 x 25 mm)
3.62 x 3.62 x 0.98 inches

Features: *high performance*
Construction: UL94V-0 PBT impeller & frame
Bearing option: ball bearing
Connection: AWG 24, UL1007 lead wires
Frame: flanged
Protection: thermal
Options: tachometer output;
 locked rotor alarm signal;



Model No.	Rated Voltage V	Current mA				Revolution RPM	Air Volume		Max. Static Pressure (H ₂)		Sound Noise dbA	Weight g
		5	12	24	48		M ³ /Min.	CFM	MM	INCH		
E9225S	5/12/24	270	98	60	-	2,000	0.82	29	2.25	0.09	24	111
E9225L	5/12/24	400	150	85	-	2,400	0.99	35	3.25	0.13	27	111
E9225M	5/12/24	560	235	125	-	2,800	1.24	44	4.75	0.19	32	111
E9225H	12/24/48	-	360	168	65	3,200	1.44	51	6.00	0.24	36	111
E9225E	12/24/48	-	498	255	85	3,600	1.58	56	7.00	0.28	39	111
E9225X	12/24/48	-	550	300	130	4,000	1.70	60	8.00	0.32	43	111